

## NTE6087 Schottky Barrier Silicon Rectifier

### **Features:**

- Guarding for Stress Protection
- Low Forward Voltage
- +150°C Operating Junction Temperature
- Guaranteed Reverse Avalanche

### **Absolute Maximum Ratings:**

|                                                                                                                                           |                |
|-------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| Peak Repetitive Reverse Voltage, $V_{RRM}$ .....                                                                                          | 45V            |
| Working Peak Reverse Voltage, $V_{RWM}$ .....                                                                                             | 45V            |
| DC Blocking Voltage, $V_R$ .....                                                                                                          | 45V            |
| Average Rectified Forward Current ( $V_R = 45V$ , $T_C = +130^\circ C$ ), $I_{F(AV)}$ .....                                               | 30A            |
| Peak Repetitive Forward Current, $I_{FRM}$<br>(Per Diode Leg, $V_R = 45V$ , Square Wave, 20kHz, $T_C = +130^\circ C$ ) .....              | 30A            |
| Non-Repetitive Peak Surge Current, $I_{FSM}$<br>(Per Diode Leg, Surge applied at rated load conditions halfwave, single phase, 60Hz) .... | 150A           |
| Peak Repetitive Reverse Surge Current (2 $\mu s$ , 1kHz), $I_{RRM}$ .....                                                                 | 1A             |
| Voltage Rate of Change ( $V_R = 45V$ ), $dv/dt$ .....                                                                                     | 1000V/ $\mu s$ |
| Operating Junction Temperature Range, $T_J$ .....                                                                                         | -65° to +150°C |
| Storage Temperature Range, $T_{stg}$ .....                                                                                                | -65° to +175°C |
| Maximum Thermal Resistance, Junction-to-Case (Per Diode Leg), $R_{thJC}$ .....                                                            | 1.5°C/W        |

### **Electrical Characteristics:** (Per Diode Leg)

| Parameter                     | Symbol | Test Conditions                             | Min | Typ | Max  | Unit |
|-------------------------------|--------|---------------------------------------------|-----|-----|------|------|
| Instantaneous Forward Voltage | $V_F$  | $i_F = 30A$ , $T_C = +125^\circ C$ , Note 1 | —   | —   | 0.73 | V    |
|                               |        | $i_F = 30A$ , $T_C = +25^\circ C$ , Note 1  | —   | —   | 0.82 | V    |
| Instantaneous Reverse Current | $i_R$  | $V_R = 45V$ , $T_C = +125^\circ C$ , Note 1 | —   | —   | 40   | mA   |
|                               |        | $V_R = 45V$ , $T_C = +25^\circ C$ , Note 1  | —   | —   | 0.2  | mA   |

Note 1. Pulse test: Pulse Width = 300 $\mu s$ , Duty Cycle  $\leq 2\%$ .

