

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet

- PDF-FQZO-12-10 P

- Part Drawings

- PDF-QuickNet SFQ ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'FQZ-12-10B'**

Your search criteria matched only one product, shown below

FQZ-12-10B



- QuickNet™ SFQ Series MTP* Fiber Optic Cassettes are compatible with QuickNet™ Patch Panels for up to 96 fiber connections in 1RU with QAPP48HDBL QuickNet™ 48-port Angled Patch Panel
- Low insertion loss of 0.5dB max. per cassette and .75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of <2.6dB
- Return loss: ≥26dB (10Gig™ multimode), ≥20dB (multimode), ≥55dB (singlemode)
- Connect together with high-density female MTP* cable assemblies as interconnecting network segments for deploying a remote or data center location in minutes
- Significantly reduce installation time and labor by eliminating field connector terminations
- Factory terminated, assembled and 100% tested
- Insertion loss data provided on every fiber cassette
- Return loss data provided on all singlemode fiber cassettes
- Lifetime traceability of test data to a Q.C. number on each fiber cassette
- 10Gig™ OM3 50/125µm Fiber Cassettes are tested per IEEE 802.3ae 10 GbE to support

network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm; backward compatible with all 50/125µm (OM2) MPO or MTP* system requirements

*MTP is a registered trademark of US Conec Ltd.

▪ Part Number	FQZ-12-10B
▪ RoHS Compliancy Status	RoHS directive is not applicable
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	Six LC duplex adapters to one male MTP*; 12-fiber pre-terminated MTP* rear mount cassette provides low insertion loss of 1.0dB max. per fiber; 10Gig™ 50/125µm (OM4) fiber. Method A, pair flipped.
▪ Pricing Description	OM4 50µm LC Duplex 6 Fiber SFQCassette, Modified Method A
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.