

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19098-0049

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite™ Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 10 (M5), 17.60mm Length

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19098

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Solderless Terminals

Product Name

Krimptite™

Type

Spade Snap

UPC

800755081510

Physical

Barrel Type

Closed

Insulation

None

Material - Plating Mating

Tin

Net Weight

0.689/g

Packaging Type

Bag

Stud Size

10 (M5)

Wire Size AWG

14, 16

Wire Size mm²

1.30 - 2.00

Material Info

Old Part Number

BB-1717-10


Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

SD-19098-004



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19098Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100
PremiumGrade™ Hand Crimp Tool	0640030100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19098-0049