



Hammers - Compact Hammers - 26 mm Heavy Duty SDS-Plus Combination Hammer with Quick Change Chuck

D25114K



D25114K Features

- Ideal for drilling anchor and fixing holes into concrete and masonry from 4 to 26 mm in diameter
- Electronic variable speed for total control in any application
- Rotation-stop for light chiselling applications in brick, soft masonry and occasionally concrete
- Impact-stop for drilling in wood, steel, ceramic and screwdriving applications
- Safety clutch eliminates sudden high-torque reaction should the bit jam
- Ergonomic rubber coated back handle design for improved comfort in use
- Rounded ergonomic industrial design allows easy and comfortable handling in any application
- Large 22 mm hammer mechanism delivers high performance with low stress to the critical components
- Improved sealing for maximum protection from dust ingress ensuring long tool life
- Output air slots designed to protect users' eye

D25114K Specifications

Power Input	800 Watts
Power Output	395 Watts
No Load Speed	0-1150 rpm
Blows per Minute	0-4300 bpm
Impact Energy	0-3.4 J
Tool Holder	SDS-Plus
Max. Drilling Capacity [Wood]	30 mm
Max. Drilling Capacity [Metal]	13 mm
Max. Drilling Capacity [Concrete]	26 mm
Max. Drilling Capacity [Core bit]	65 mm
Weight	2.8 kg
Length	368 mm
Height	200 mm

D25114K Standard

- Multi-position side handle
- Depth stop
- "Quick Change" 13 mm 3 jaw keyless chuck
- Heavy duty carrying case