


CRZ 1362

RoHS COMPLIANT




C1

Har-Flex 26P female connector

C2

Har-Flex 26P female connector



Part-No. / 产品号码	Length/长度
33 15 243 050 0009 .00	500±5
33 15 243 020 0008 .00	200±3
33 15 243 010 0007 .00	100±3
33 15 243 027 0034 .00	270±3

NOTES/要求:

- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.
- 2.) CABLE OPERATION TEMPERATURE= -30° C TO +105° C .
- 3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION
HARTING P/N & REVISION

Rev.	Description	Appr.	Date
01	Add side view.	Lucy.Z	15/04/13
00	Prototype	Andrew.H	25/09/12

Free size tol.				V=		cm ³ / A=		cm ²		Title	
All Dimensions in mm Original Size DIN A4				Name	Date	Scale	Sheet	1 of 1		Har-Flex female 26pole, double ended	
				Detail						Flat cable assembly, L=xMM	
				Insp.							
				Approved							
HARTING (Zhuohai) Manufacturing Co., Ltd										DWG. TB_33 15 0003 .01	
HARTING										No.	