



Rev	AWO #	Description	Date	Appr
-		RELEASED	11/08/04	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

- Material: Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating: Operating temperature: -55°C to +105°C
Packaging: Anti-ESD plastic tubes

A = .100 [2.54] X No. of Positions Per Row
Positions available: 20, 24, 28, 32, 40 & 48

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 .XX ± .020 .XXX ± .015		HOLE ØX ± .10 ØXX ± .015 ØXXX ± .010		DATE	
DRAWN		SS		11/08/04	
CHECKED					
APPROVED					
TITLE		IC SOCKET, .600 ROW CENTERS, PCB, TIN PLATED			
ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
SIZE		PART NO.		REV.	
X		ICS-6XX-T		-	
REF:		SCALE: NTS		SHEET 1 OF 1	