

VC-MEMV-T3-R-M25

Order No.: 1886618

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1886618>

Sleeve housing with EMC coating and conductive seal, with metric cable entry, locking screws with knurled head, type 3

Commercial data

GTIN (EAN)	4017918848033
Note	Made-to-order
sales group	D201
Pack	5 pcs.
Customs tariff	85389099
Weight/Piece	0.36208 KG
Catalog page information	Page 367 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Design	VC3
Height	75 mm
Width	33 mm
Length	89 mm
Housing type	Sleeve housings
Color	nickel
Locking type	Screw locking, knurled head
Tightening torque, mounting screw	1.5 Nm ± 0.3 Nm
No. of cable exits	1
Cable exit	Lateral
Type of the screw connection	Metric, M25
Pg screw connection	None
Degree of protection	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Zinc die-cast, surface bronzed and nickel-plated
Housing surface material	Nickel-plated
Seal material	EPDM, conductive
Material of locking screw	Nickel-plated brass

Certificates / Approvals



Certification


GOST

Accessories

Item	Designation	Description
Marking		
1852875	VC-BZS WH	Marker labels, unprinted, 5-section, for individual labeling with M-PEN or CMS system, white

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;