



FK12M

Pointed tip tapered penetration probe



Copyright © 2007 Test Products International, Inc.

Application

Heavy duty penetration into
semi-solids and liquids tapered
shaft resist bending

Range°F°C

-58° to 500°F
-50° to 250°C

Probe tip

21

Dimensions

Stem Length: 11.8" (300mm)
Diameter: 0.25 / 0.10"
(6.4 / 2.5mm)
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane