

Wiha 3K Series Screwdrivers and Sets



460 95 Set 5 Pcs. Slotted & Phillips

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item No.	Slotted Size (mm)	Slotted Size (mm)	Phillips Size (mm)	Phillips Size (mm)	Weight (lbs.)	
460 95	450 55	4.5	100	451 35 0	60	1.04
	450 60	6.0	100	451 37 1	80	Each
				451 42 2	100	\$21.94



460 94 Set 6 Pcs. Slotted & Phillips

Blade chrome-vanadium-molybdenum steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item No.	Slotted Size (mm)	Slotted Size (mm)	Phillips Size (mm)	Phillips Size (mm)	Weight (lbs.)	
460 94	450 50	3.0	100	451 37 1	80	.91
	450 55	4.5	100	451 44 2	150	
	450 58	5.5	125			Each
	450 65	6.5	150			\$26.48



460 97 Set 8 Pcs. Slotted & Phillips Blade CVM steel, chrome nickel-plated. Wiha-3k Ergo handle, cushion grip. Precision black tips.

Item No.	Slotted Size (mm)	Slotted Size (mm)	Phillips Size (mm)	Phillips Size (mm)	Weight (lbs.)	
460 97	450 50	3.0	100	451 37 1	80	1.70
	450 55	4.5	100	451 42 2	100	
	450 60	6.0	100	451 50 2	40	Each
	450 67	8.0	150	451 52 3	150	\$40.54



452 Pozidriv® Screwdriver, With Wiha-3K Series Handle

Blade chrome-vanadium-molybdenum steel, hard chromed shaft. Wiha-3k Ergo handle, cushion grip. Black tip.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
452 05	0	60	2.3	146	5.7	.06	10	\$3.00
452 07	0	100	3.9	186	7.3	.07	10	\$3.00
452 15	1	80	3.1	187	7.3	.13	10	\$4.14
452 20	1	100	3.9	207	8.1	.14	10	\$4.14
452 25	2	100	3.9	219	8.6	.21	10	\$5.50
452 30	2	150	5.9	269	10.6	.23	10	\$6.12
452 35	3	150	5.9	269	10.6	.31	10	\$7.26



451 Phillips Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
451 62	1	80	3.1	187	7.3	.14	1	\$4.02
451 64	1	200	8.0	307	12.0	.17	1	\$4.94
451 65	2	100	4.0	218	8.5	.22	1	\$5.36
451 66	2	150	6.0	268	10.5	.24	1	\$5.58
451 67	2	200	8.0	318	12.5	.26	1	\$7.64
451 71	3	150	6.0	268	10.5	.32	1	\$6.82



450 Slotted Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	Each
450 23*	4.0	.157	100	4.0	0.8	.031	206	8.1	.13	1	\$4.12
450 24	4.5	.177	100	4.0	1.0	.039	207	8.1	.14	1	\$3.80
450 25	4.5	.177	150	6.0	1.0	.039	257	10.1	.15	1	\$4.54
450 26	4.5	.177	200	8.0	1.0	.039	306	12.0	.16	1	\$4.84
450 27	5.5	.216	125	5.0	1.0	.039	243	9.5	.20	1	\$4.22
450 28	6.0	.236	100	4.0	0.9	.035	218	8.5	.21	1	\$4.74
450 29	6.0	.236	150	6.0	0.9	.035	268	10.5	.24	1	\$5.26
450 30	6.0	.236	200	8.0	0.9	.035	318	12.5	.26	1	\$5.46
450 33	8.0	.315	150	6.0	1.2	.047	268	10.5	.27	1	\$6.82
450 34	10.0	.393	200	8.0	1.6	.063	318	12.5	.36	1	\$7.14

* Cabinet Tip



455 TORX® Screwdriver, With Wiha-3K Series Handle & Hanger

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.	Each
455 57	T15	80	4.0	190	7.5	.12	1	\$4.12
455 58	T20	100	4.5	215	8.4	.12	1	\$4.32
455 59	T25	100	4.5	215	8.4	.21	1	\$4.64
455 60	T27	115	5.1	240	9.4	.29	1	\$5.16
455 62	T30	115	6.0	233	9.1	.32	1	\$5.78