


**DESCRIPTION: MALE CENTRONICS BACKSHELL KIT**

- BACKSHELL KIT INCLUDES:**
- (1) SOLDER CUP CONNECTOR
  - (1) BACKSHELL WITH STRAIN RELIEF, (2) SCREWS
  - (1) FACE PLATE
  - (1) RUBBER GROMMET



**WILL ACCEPT 26-20 AWG WIRE**

**110-YYY-103L001**

**SERIES** \_\_\_\_\_

**POSITIONS** \_\_\_\_\_

014 \_\_\_\_\_

024 - NOT AVAILABLE \_\_\_\_\_

036 \_\_\_\_\_

050 \_\_\_\_\_

**GENDER** \_\_\_\_\_

1 = MALE \_\_\_\_\_

2 = FEMALE \_\_\_\_\_

**TERMINATION** \_\_\_\_\_

0 = SOLDER CUP \_\_\_\_\_

**SHELL PLATING** \_\_\_\_\_


3 = NICKEL \_\_\_\_\_

**HARDWARE OPTIONS** \_\_\_\_\_

00 = NOT AVAILABLE \_\_\_\_\_

**PLATING OPTIONS** \_\_\_\_\_

1 = GOLD FLASH \_\_\_\_\_



	A	B	C	D
014	1.496	1.132	1.572	.622
	38.00	29.75	40.06	15.80
024	1.919	1.593	1.560	.622
	48.75	40.45	39.61	15.80
036	2.431	2.090	1.624	.622
	61.76	53.10	41.25	15.80
050	3.026	2.677	1.730	.622
	76.86	68.00	43.95	15.80

**MATERIALS:**

**INSULATOR: GLASS-FILLED THERMOPLASTIC**  
UL RATED 94V-0 - 230°C PROCESS TEMP.

**CONTACTS: COPPER ALLOY**

**SHELL: STEEL, NICKEL PLATED**

**RoHS COMPLIANT**

**ELECTRICALS:**

**CONTACT CURRENT RATING: 5 AMPS**

**DIELECTRIC WITHSTANDING VOLTAGE: AC 1200 R.M.S.**

**INSULATION RESISTANCE: 1000 mohms MINIMUM AT 500V DC**

**CONTACT RESISTANCE: 30 mOHMS MAXIMUM**

**OPERATING TEMPERATURE: -55°C TO +125°C**

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: <b>WAYNE ROBBINS</b>	DATE: <b>7-15-05</b>
	<h1>NorComp</h1>		CHECKED:	DATE:
SCALE: 1:1			SHEET <b>1</b>	OF <b>1</b>
		DWG NO. <b>110-YYY-103L001</b>		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[110-014-103L001](#) [110-036-103L001](#) [110-050-103L001](#) [110-024-103L001](#)