

SERIES 04

4PST

FEATURES


- Joy Stick Action
- Position Locator On CRT Screens
- Moves Cursor On Menu Display



DIMENSIONS In Inches (and millimeters)


Basic Switch

04A




Bat Handle

04A-B01



Keycap

04A-K01



SPECIFICATIONS

Rating Criteria

Rated: Make and break 250 mA at 115 Vac or 125 mA at 220 Vac resistive load for 500,000 operations

Contact Resistance: 25 milliohms maximum on a new switch

Insulation Resistance: 1,000 megohms at 100 Vdc

Dielectric Strength: 500 Vac RMS minimum

Operating Temperature: -40°C to +85°C

Materials and Finishes

Base, Cover and Switch Actuator: Polyester (Black)

Terminals: Brass, gold-plated over nickel

Shorting Bar: Phosphor bronze, gold-plated over nickel


Spring: Tinned music wire

Keycap: ABS or equivalent

Bat-Handle: ABS

CIRCUITRY

Footprint



ORDERING INFORMATION

Description	Part No.
Basic Switch	04A
Switch with Arrowhead Keycap	04A-K01
Switch with Bat-Handle	04A-B01*

*Shipped with bat handle permanently attached.

Available from your local Grayhill Distributor.
For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.