

High-voltage Switching Transistor

(Telephone power supply) (−400V, −0.5A)

2SA1812 / 2SA1727 / 2SA1776

●Features

- 1) High breakdown voltage, $BV_{CEO} = -400V$.
- 2) Low saturation voltage, typically $V_{CE(sat)} = -0.3V$ at $I_C / I_E = -100mA / -10mA$.
- 3) High switching speed, typically $t_f = 1 \mu s$ at $I_C = -100mA$.
- 4) Wide SOA (safe operating area).

●Packaging specifications and hFE

Type	2SA1812	2SA1727	2SA1776
Package	MPT3	CPT3	ATV
hFE	PQ	PQ	PQ
Marking	AJ*	—	—
Code	T100	TL	TV2
Basic ordering unit (pieces)	3000	3000	2500

* Denotes hFE

●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Collector-base breakdown voltage	BV_{CBO}	−400	—	—	V	$I_C = -50 \mu A$
Collector-emitter breakdown voltage	BV_{CEO}	−400	—	—	V	$I_C = -1mA$
Emitter-base breakdown voltage	BV_{EBO}	−7	—	—	V	$I_E = -50 \mu A$
Collector cutoff current	I_{CBO}	—	—	−1	μA	$V_{CB} = -400V$
Emitter cutoff current	I_{EBO}	—	—	−1	μA	$V_{EB} = -6V$
DC current transfer ratio	hFE	82	150	270	—	$V_{CE} = -5V$, $I_C = -50mA$
Collector-emitter saturation voltage	$V_{CE(sat)}$	—	—	−1	V	$I_C / I_E = -100mA / -10mA$
Base-emitter saturation voltage	$V_{BE(sat)}$	—	—	−1.2	V	$I_C / I_E = -100mA / -10mA$
Transition frequency	f _T	—	12	—	MHz	$V_{CB} = -5V$, $I_E = 50mA$, $f = 5MHz$
Output capacitance	C _{ob}	—	18	—	pF	$V_{CE} = -10V$, $I_E = 0A$, $f = 1MHz$
Turn-on time	t _{on}	—	0.6	—	μs	$I_C = -100mA$, $R_L = 1.5k \Omega$
Storage time	t _{sig}	—	2.7	—	μs	$I_{B1} = -I_{B2} = -10mA$
Fall time	t _f	—	1	—	μs	$V_{CC} = -150V$

●Absolute maximum ratings (Ta=25°C)

Parameter	Symbol	Limits	Unit
Collector-base voltage	V_{CBO}	−400	V
Collector-emitter voltage	V_{CEO}	−400	V
Emitter-base voltage	V_{EBO}	−7	V
Collector current	I_C	−0.5	A (DC)
		−1.0	A (Pulse) *1
Collector power dissipation	P_C	0.5	W
		2	W *2
		1	W
		10	W (Tc=25°C)
		1	W *3
Junction temperature	T _J	150	°C
Storage temperature	T _{stg}	−55~+150	°C

*1 Single pulse *2 When mounted on a 40×40×0.7mm ceramic board.

*3 When t = 1.7mm and the foil collector area on the PC board is 1cm² or greater.

(96-609-A313)