



Ceramic Disc Capacitors Class 1, 500 V (DC) Narrow Tolerance

FEATURES

- Low losses
- High stability
- High capacitance in small size
- Kinked (preferred) or straight leads
- Lead (Pb)-free available




APPLICATIONS

- Bypassing
- Coupling
- Resonant circuit.

DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors have inward kinked leads with a spacing of 5 mm (0.200") and a lead length from 4 to 30 mm. Encapsulation is made of phenolic resin.



Capacitors with 5 mm (0.20") lead spacing.

CAPACITANCE RANGE:

Class 1, at 1 MHz, 1.2 V (RMS); 1.0 pF to 330 pF
1 kHz, $1 \pm 0.2V$ (RMS) for capacitance values higher than 1000 pF.

RATED DC VOLTAGE:

500 V

DIELECTRIC STRENGTH:

250 % of rated voltage

INSULATION RESISTANCE AT 500V (DC):

$\geq 10\,000\text{ M}\Omega$

TOLERANCE ON CAPACITANCE:

$\pm 0.25\text{ pF}$; $\pm 2\%$

DISSIPATION FACTOR:

Class 1, $C \leq 30\text{ pF}$; $\leq 20 \times (10/C + 0.7) \times 10^{-4}$ maximum

Class 1, $C > 30\text{ pF}$; $\leq 20 \times 10^{-4}$

TEMPERATURE COEFFICIENTS:

Class 1 NP0; P100; N150; N750; N1500

SECTIONAL SPECIFICATIONS:

Class 1 IEC 60 384-8,
EIA 198

CLIMATIC CATEGORY:

Class 1 55/125/21

OPERATING TEMPERATURE RANGE:

Class 1 - 55 to + 125 °C

MARKING

Marking indicates capacitance value and tolerance in accordance with "EIA 198".

The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of $25 \pm 3\text{ }^{\circ}\text{C}$, at normal atmospheric conditions

HV 500 V Narrow Tolerance

Vishay BCcomponents

Ceramic Disc Capacitors
Class 1, 500 V (DC) Narrow Tolerance



ORDERING INFORMATION, CLASS 1, 500 V (DC), KINKED										
C (pF)	TOL. (%)	D _{max} (mm)	LEAD SPACING F (mm)	SH ⁽²⁾ (mm)	CLEAR TEXT CODE	PACKAGING CODE 8 th AND 9 th DIGIT ⁽³⁾			CATALOG NUMBER ⁽⁴⁾ 3 rd DIGIT: 5 = STANDARD, 8 = RoHS COMPLIANT	
					13 th DIGIT: T = REEL; U = AMMO; 3 = BULK 16 th DIGIT: R = RoHS COMPLIANT	REEL	AMMO	BULK		
CLASS 1 P100										
1.5	± 0.25	5.0	5.0	4.0	D159C20M7GL6.J5.	06	08	10	22.2 598 ..144	
2.2					D229C20M7GL6.J5.				22.2 598 ..244	
3.3					D339C20M7GL6.J5.				22.2 598 ..344	
4.7					D479C20M7GL6.J5.				22.2 598 ..444	
6.8	± 2 %	6.5			D689C25M7GL6.J5.				22.2 598 ..644	
10		7.5			D100G29M7GL6.J5.				22.2 598 ..004	
15		8.5			D150G33M7GL6.J5.				22.2 598 ..104	
22		10.0			D220G39M7GL6.J5.				22.2 598 ..204	
33		12.0			D330G47M7GL6.J5.				22.2 598 ..304	
CLASS 1 NP0										
1.0	± 0.25	5.0	5.0	4.0	D109C20C0KL6.J5.	06	08	10	22.2 508 ..044	
1.5					D159C20C0KL6.J5.				22.2 508 ..144	
2.2					D229C20C0JL6.J5.				22.2 508 ..244	
3.3					D339C20C0JL6.J5.				22.2 508 ..344	
4.7					D479C20C0HL6.J5.				22.2 508 ..444	
6.8					D689C20C0HL6.J5.				22.2 508 ..644	
10	± 2 %				6.5				D100G20C0GL6.J5.	22.2 508 ..004
15									D150G20C0GL6.J5.	22.2 508 ..104
22									D220G25C0GL6.J5.	22.2 508 ..204
33									D330G25C0GL6.J5.	22.2 508 ..304
47		D470G29C0GL6.J5.							22.2 508 ..404	
68		D680G33C0GL6.J5.							22.2 508 ..604	
100		D101G39C0GL6.J5.							22.2 508 ..014	
150		D151G47C0GL6.J5.							22.2 508 ..114	
CLASS 1 N150										
2.2	± 0.25	5.0	5.0	4.0		D229C20P2JL6.J5.	06	08	10	22.2 518 ..244
3.3					D339C20P2JL6.J5.	22.2 518 ..344				
4.7					D479C20P2HL6.J5.	22.2 518 ..444				
6.8					D689C20P2HL6.J5.	22.2 518 ..644				
10	± 2 %				6.5	D100G20P2GL6.J5.				22.2 518 ..004
15						D150G20P2GL6.J5.				22.2 518 ..104
22						D220G25P2GL6.J5.				22.2 518 ..204
33		D330G25P2GL6.J5.				22.2 518 ..304				
47		D470G29P2GL6.J5.				22.2 518 ..404				
68		D680G33P2GL6.J5.				22.2 518 ..604				
100		D101G43P2GL6.J5.				22.2 518 ..014				



HV 500 V Narrow Tolerance

Ceramic Disc Capacitors
Class 1, 500 V (DC) Narrow Tolerance

Vishay BCcomponents

ORDERING INFORMATION, CLASS 1, 500 V (DC), KINKED									
C (pF)	TOL. (%)	D _{max} (mm)	LEAD SPACING F (mm)	SH ⁽²⁾ (mm)	CLEAR TEXT CODE	PACKAGING CODE 8 th AND 9 th DIGIT ⁽³⁾			CATALOG NUMBER ⁽⁴⁾ 3 rd DIGIT: 5 = STANDARD, 8 = RoHS COMPLIANT
					13 th DIGIT: T = REEL; U = AMMO; 3 = BULK 16 th DIGIT: R = RoHS COMPLIANT	REEL	AMMO	BULK	
CLASS 1 N750									
6.8	± 0.25	5.0	5.0	4.0	D689C20U2JL6.J5.	06	08	10	22.2 558 ..644
10	± 2 %				D100G20U2JL6.J5.				22.2 558 ..004
15					D150G20U2JL6.J5.				22.2 558 ..104
22					D220G20U2JL6.J5.				22.2 558 ..204
33		6.5			D330G25U2JL6.J5.				22.2 558 ..304
47		7.5			D470G29U2JL6.J5.				22.2 558 ..404
68		8.5			D680G33U2JL6.J5.				22.2 558 ..604
100		10.0			D101G39U2JL6.J5.				22.2 558 ..014
150		12.0			D151G47U2JL6.J5.				22.2 558 ..114
CLASS 1 N1500									
8.2	± 0.25 pF	5.0	5.0	4.0	D829C20P3KL6.J5.	06	08	10	22.2 588 ..844
10	± 2 %				D100G20P3KL6.J5.				22.2 588 ..004
15					D150G20P3KL6.J5.				22.2 588 ..104
22					D220G20P3KL6.J5.				22.2 588 ..204
33					D330G20P3KL6.J5.				22.2 588 ..304
47					D470G20P3KL6.J5.				22.2 588 ..404
68		6.5			D680G25P3KL6.J5.				22.2 588 ..604
100		7.5			D101G29P3KL6.J5.				22.2 588 ..014
150		8.5			D151G33P3KL6.J5.				22.2 588 ..114
220	10.0	D221G39P3KL6.J5.			22.2 588 ..214				
330	12.0	D331G47P3KL6.J5.			22.2 588 ..314				


Notes

- Maximum thickness 4.0 mm.
- SH = seated height.
- Packaging codes refer to inward kinked leads. Other styles available on request.
- 3rd digit to complete RoHS catalog number. 8th and 9th digit of the catalog number to be completed with the packaging code.
- Other capacitance values E12 series available

PACKAGING				
D _{max} (mm)	SIZE CODE	PACKAGING QUANTITIES		
		BULK	REEL	AMMO
5.0 (0.20")	20	1000	2000	2000
6.5 (0.25")	25			
7.5 (0.29")	29			
8.5 (0.33")	33			
10.0 (0.39")	39			
11.0 (0.43")	43			
12.0 (0.47")	47			

Note

- The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel or in ammopack.



Kinked capacitors on tape, lead spacing 5.0 mm (0.2").


DIMENSIONS OF TAPE			
SYMBOL	PARAMETER	DIMENSIONS (mm)	
		NOMINAL	TOLERANCE
D	body diameter	11.0 maximum	-
d	lead diameter	0.6	± 0.05
P	pitch between capacitors	12.7	± 1.0
P ₀	feed-hole pitch	12.7	± 0.3; note 1
ΔP	plane deviation	1.0 maximum	-
P ₁	feed-hole centre to lead centre	3.85	± 0.7; note 2
P ₂	feed-hole centre to component centre	6.35	± 1.3; note 2
F	lead spacing	5.0	+ 0.6 - 0.4
Δh	component alignment	0	± 1.0
Δs	deviation along tape, left or right	0	± 1.0
W	tape width	18.0	+ 1.0 - 0.5
W ₀	hold-down tape width	5.0 minimum	-
W ₁	hole position	9.0	+ 0.75 - 0.5
W ₂	hold-down tape margin	3.0 maximum	-
H ₀	height to seating plane	16.0	± 0.5
H ₁	maximum component height	32.0	-
e	lead end protrusion	1.0 maximum	-
L	maximum length of snapped lead	11.0	-
D ₀	feed-hole diameter	4.0	± 0.2
t	total tape thickness	0.9 maximum	-
t ₁	maximum thickness of tape and wires	1.5 maximum	-

Notes


1. Cumulative pitch error: $\pm \leq 1$ mm /20 pitches.
2. Obliquity maximum 3°.



REEL AND TAPE DATA in millimeters



Reel with capacitors on tape.



Ammopack with capacitors on tape.



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.