

Cable marker label - WML 14 (25X19)R YE - 0817549

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker label, Roll, yellow, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Adhesive, Cable diameter: ≤14 mm, Lettering field: 25 x 19 mm

Why buy this product

- ✓ The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- ✓ High-quality labeling image created by thermal transfer printing
- ✓ Quick and easy handling
- ✓ Resistant to solvents
- ✓ The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- ✓ The cable marker labels consist of a labeling field and a transparent protective foil

Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 160 (CL2-2011)
GTIN	 4 046356 125581
Weight per Piece (excluding packing)	800.7 GRM
Country of origin	GERMANY

Technical data

General

Length (b)	63.5 mm
Width (a)	25.4 mm
Color	yellow
Base element material	Vinyl film
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 70 °C
Components	Silicone-free
Material	PVC
Number of individual labels	1500
Number of individual labels per row	3

Cable marker label - WML 14 (25X19)R YE - 0817549

Classifications

eclass

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103
eCl@ss 6.0	27400401

etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black