



LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	86				M	REV PER 0G3A-0561-01	090CT02	JR/MS



- 1 CIRCULAR MIL AREA RANGE: 325-375 MCM
2 TIN PL 0.00381 [.000150] MIN THK PER ASTM B 545
3 CLEANED, UNPLATED

3	327287-3
2	327287
FINISH	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± -	DR 02/28/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK 23JAN95 MS FEHER		
MATERIAL ANNEALED COPPER ASTM B-75	APPD 23JAN95 WJ VOCKROTH	NAME TERMINAL, AMPPOWER™ WIRE SIZE: 350 MCM	
	APPD 23JAN95 TL SHUTTER		
FINISH SEE TABLE	PRODUCT SPEC 108-30200	SIZE C	CAGE CODE 00779
	APPLICATION SPEC -	SCALE 1:1	DRAWING NO 327287
	WEIGHT .031 LB		SHEET 1 OF 1

METRIC