

Item # ATV312HU15N4, Variable Speed Drive



Variable Speed Drive
Variable Speed Drive

SPECIFICATIONS

Family	Altivar 312
Product Line	AC Drives
Output Ampere Rating	4.1
Application	Constant Torque
Enclosure Rating	IP20
Frame Size	6
HP Rating	2
kW Rating	1.5
Voltage Rating	400/480VAC
Input Phase	3 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	6
Analog Input	3

Analog Output	1
Logic/Relay Outputs	1 Form C, 1 NO
Weight [lb]	2.98
Weight [kg]	1.35
UL File No.	E116875
CSA File	1464725
Other	CE, GOST, RoHS, NOM, EMITECH
Communication	Modbus and CANopen

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312HU15N4](#)