



Combination spanner, offset, 111M

Combination spanner, offset in Metric sizes.

DIN 3113 / ISO 3318 / ISO 7738


Finish: nickel and chrome-plated, fine-polished.

Material: VANADIUM-EXTRA.

Open-end angle 15°, ring end 15° angled, equal openings at both ends, short type.

With Dynamic-Drive-Profile.

SB = Retail packed on a plastic info card.



	 731415+			L mm	a1xa2 mm	b1xb2 mm	
111M-5.5	1828608	10	5.5	105	5.0x3.2	9.5x14	12
111M-6	1828615	10	6	105	5.0x3.2	10.0x14	13
111M-7	1828622	10	7	110	5.6x3.5	11.0x17	18
111M-8	1828639	10	8	110	5.6x3.5	12.0x18	18
111M-9	1828646	10	9	120	6.0x3.8	13.8x20	22
111M-10	1828653	10	10	135	6.6x4.2	15.0x22	30
111M-11	1828660	10	11	135	6.6x4.2	16.5x23	30
111M-12	1828677	10	12	150	7.4x4.7	18.0x26	45
111M-13	1828684	10	13	160	7.4x4.7	19.5x28	45
111M-14	1828691	10	14	168	8.2x5.3	20.6x31	65

111M-15	1828707	10	15	170	8.2x5.3	22.0x32	65
111M-16	1828714	10	16	178	8.8x5.6	23.4x34	80
111M-17	1828721	10	17	190	9.4x6.0	24.8x37	110
111M-18	1828738	10	18	210	10.0x6.3	26.4x39	115
111M-19	1828745	10	19	220	10.0x6.3	27.6x40	120
111M-20	1828752	10	20	232	11.0x7.0	29.0x42	150
111M-21	1828769	10	21	250	11.0x7.0	30.4x44	150
111M-22	1828776	5	22	255	12.0x7.7	31.8x48	200
111M-23	1828783	5	23	255	12.0x7.7	33.4x48	210
111M-24	1828790	5	24	280	13.0x8.4	34.6x50	265
111M-25	1828806	5	25	280	13.0x8.4	36.0x51	270
111M-26	1828813	5	26	280	13.0x8.4	37.5x53	270
111M-27	1828820	5	27	310	14.0x9.2	38.8x57	350
111M-28	1828837	5	28	310	14.0x9.2	40.5x58	365
111M-29	1828844	5	29	310	14.0x9.2	41.0x58	380
111M-30	1828851	5	30	355	15.0x10.0	43.5x62	480
111M-32	1828868	5	32	360	15.0x10.0	46.0x65	500
111M-34	1828875	5	34	380	15.0x10.0	47.0x65	500
111M-36	0135516	1	36	410	19.4x13.5	53x74	800
111M-41	0135523	1	41	460	21.6x16	61x84	1160
111M-46	0135530	1	46	500	23x17	66x92	1700
111M-50	0135547	1	50	540	24.6x18	73x102	2000
111M-55	0135554	1	55	560	21.5x28	86x118	2800
111M-60	0135561	1	60	600	23.5x30	94x126	3900
111M-65	0135578	1	65	680	25x32	108x148	5800
111M-70	0135585	1	70	680	25x32	108x148	5800
111M-75	0135592	1	75	730	25x35	115x155	6500
111M-80	0135608	1	80	730	25x35	115x155	6500
		1					