

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200980181

Status:

Active

Overview:

PROFIBUS Solutions

Description:

PROFIBUS Straight D-Sub to Micro-Change (M12) Double Ended Cordset, 5 Poles, Male (90°), 22 AWG, PUR Cable, 1.0m (3.28') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Cordsets

Series

120098

Connector End A

D-Sub (9-pin)

Connector End B

Micro-Change (M12)

IP Rating

IP40, IP67

Material - Contact

Copper Alloy

Overview

PROFIBUS Solutions

Product Name

Micro-Change (M12), PROFIBUS

Protocol

EtherNet

Region

America, Asia, Europe

Type

Double Ended

UPC

78172504291

Physical

Cable Diameter

8.00mm (.315")

Cable Length

1.0m (3.28')

Color - Cable Jacket

Purple

Coupling Style

Threaded

Gender

Male-Female/Male

Keyway

N/A

LED Indicator

No

Material - Cable Jacket

PUR

Material - Connector Body

PUR

Material - Coupling Nut

Nickel-plated Brass

Material - Plating Mating

Gold

Orientation

90° to 90°/90°

Poles

5

Temperature Range - Operating

-20°C to +80°C

Wire Size AWG

22

Wire/Cable Type

Twisted Pair

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC/DC

Material Info

Engineering Number

BP5S63PP4M010

Reference - Drawing Numbers

Sales Drawing

SD-120098-004



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION