


REVISIONS		DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. 880							
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
141	A	RELEASED		JWM	3/15/02	HO	3/15/02	DJC	3/15/02



NOTES:

- Material: Nylon 6/6 - Natural
- Bundle Diameter: 1/16" to 1 3/4"
- Minimum Loop Tensile Strength: 40 lbs.[18.14 kg]
- Flammability Rating: UL94 Class V2
- Operating Temperature: -40°F to 185°F [-40°C ~ 85°C]

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION
AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE
BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE
INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

 **SPC TECHNOLOGY**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:		ELECTRONIC FILE			REV
	Jeff McVicker	3/15/02	SIZE	DWG. NO.	1703	92N3613.dwg	A	
	Checked By:	Date:						
	Hisham Odish	3/15/02						
	Approved By:	Date:	SCALE:	U.O.M.:	INCHES [mm]			
	Daniel Carey	3/15/02	NTS					