


**109-00097**

Q Tie, 6.3" Long, 30lb Tensile Strength, PA66HS, Black, 100/pkg

Article Number: 109-00097



Part Number: 109-00097

Type: Q30R

**Base Data**

|                                      |                                                                                                                                                                                                                                                                                                                                                 |
|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Part No.</b>                      | 109-00097                                                                                                                                                                                                                                                                                                                                       |
| <b>Type</b>                          | Q30R                                                                                                                                                                                                                                                                                                                                            |
| <b>Color</b>                         | Black (BK)                                                                                                                                                                                                                                                                                                                                      |
| <b>Features</b>                      | <ul style="list-style-type: none"><li>• Open-head design with easily detectable slot opening allows for swift and easy insertion</li><li>• Pre-lock feature allows for a temporary hold</li><li>• The large ribbed tail permits an ergonomic installation</li><li>• Two rails on the strap ensure guidance through the cable tie head</li></ul> |
| <b>Identification Plate Position</b> | none                                                                                                                                                                                                                                                                                                                                            |
| <b>Releasable Closure (Yes/No)</b>   | No                                                                                                                                                                                                                                                                                                                                              |
| <b>Tie Closure</b>                   | plastic pawl                                                                                                                                                                                                                                                                                                                                    |
| <b>Variant</b>                       | Inside Serrated                                                                                                                                                                                                                                                                                                                                 |

**Product Dimensions**

|                              |                |
|------------------------------|----------------|
| <b>Min. Tensile Strength</b> | 30.0lbs / 130N |
| <b>Length (L)</b>            | 6.3" / 160mm   |
| <b>Width (W) (imperial)</b>  | 0.14"          |
| <b>Width (W)</b>             | 3.6mm          |
| <b>Min. Ø Bundle</b>         | 0.06" / 3.0mm  |
| <b>Max. Ø Bundle</b>         | 1.5" / 38.0mm  |
| <b>Thickness</b>             | 1.3mm          |

**Material and Specifications**

|                 |                                        |
|-----------------|----------------------------------------|
| <b>Material</b> | Polyamide 6.6 heat stabilized (PA66HS) |
|-----------------|----------------------------------------|

|                               |                                                                                   |
|-------------------------------|-----------------------------------------------------------------------------------|
| <b>Flammability</b>           | UL94 V2                                                                           |
| <b>Halogenfree</b>            | YES                                                                               |
| <b>Material Specification</b> | RoHS                                                                              |
| <b>Operating Temperature</b>  | -40 °F to +221 °F (-40 °C to +105 °C)                                             |
| <b>ROHS Conformity</b>        |  |

### Logistic and Packaging

---

|                       |               |
|-----------------------|---------------|
| <b>Packaging Type</b> | bag           |
| <b>Pkg. Qty.</b>      | 100           |
| <b>Carton Qty.</b>    | 12000Pieces   |
| <b>EAN code</b>       | 4031026410333 |

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)  
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512