

规格 Specifications

额定负荷 Ratings	DC 30 V 100mA
初始接触电阻 Initial Contact Resistance	200 mΩ Max.
绝缘电阻 Insulation Resistance	DC250V 60 Sec. 10 MΩ Min.
抗电强度 Dielectric Voltage	AC 250 V (50~60Hz) 60 Sec.
操作力 Operation Force (gf)	30±20 gf
自由位置 Free Position	5.20mm Max
动作位置 Operation Position	3.20±0.40mm
超行程 Over Travel	2.00±0.40mm
负荷寿命 Operation Life With Load	20,000 Cycles





示意图 SCHEMATIC

安装孔 PIERCING PLAN

7	端子 TERMINAL	C2680R ⑥	3	Ag PLATED	A03	零件材料标示变更见⑥	曹文斌	2006-03-20
6	胶壳 HOUSING	PA46 ⑥	1	BLACK C		机械寿命变更为负荷寿命见⑥		
5	弹簧 SPRING ⑥	SUS	1	NATURAL		追加零件标示见⑥		
4	接触片 CONTACT CLIP ⑥	C5210R	1	Ag CLAD	A02	PA 1300G011 变更为 PA46 TE250F6-BK 见 ⑥	曹文斌	2006-01-21
3	滑块 SLIDER ⑥	PBT	1	BLACK C		3.30 变更为 3.70 见 ⑥		
2	胶盖 COVER	PA46 ⑥	1	BLACK C	A01		曹文斌	2005-12-30
1	胶柄 KNOB	POM ⑥	1	BLACK C	标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
序号 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS		DWG NO. ITEM2383		

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE		DETECTOR SWITCH		ITEM NO	DS-080-C PA		
UNDER 1	± 0.10	DRAWN	曹文斌	2006-03-20	VERSION	A03	PAGE 1 OF 1		
1 - 10	± 0.30	REVIEWED	张念明	2006-03-20	SCALE	NO SCALE	UNIT	mm	
OVER 10	± 0.50	APPROVED	林高全	2006-03-21	PROJECTION				

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[DS-080-C PA](#)