

SPECIFICATIONS




PARAMETERS	VALUES	UNIT
RATED INPUT VOLTAGE	3	Vrms
MAX INPUT VOLTAGE	20	Vp-p
MINIMUM OUTPUT SPL @ 3Vrms/10CM (AT 1.0, 1.2, 1.5, 2.0 kHz)	75	dBA
RESONANT FREQUENCY	1,400 ± 20%	Hz
FREQUENCY RANGE	300 ~ 20,000	Hz
HOUSING MATERIAL	STAINLESS STEEL	-
OPERATING TEMPERATURE	-20 ~ +60	°C
WEIGHT	1.3	grams

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO
PROJECTS UNLIMITED, INC. ANY USE OR
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR
WRITTEN PERMISSION OF PROJECTS UNLIMITED,
INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.


REVISION HISTORY			
ITP	DESCRIPTION	DATE	APPROVED

LTR	DESCRIPTION	DATE	APPROVED
-	RELEASED FROM ENGINEERING	2/9/2010	
A	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	5/25/2010	B.R.
B	REVISED MAX INPUT VOLTAGE	6/1/2011	B.R.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.	SIZE A3	Designed by	Date	Checked by	Date	Approved by	Date	Drawn Date
		B.R.	2/9/2010	C.W.	2/9/2010	B.R.	2/9/2010	5/25/2010
APS2714S-R.idw		 pui audio TM a projects unlimited company	APS2714S-R					
			Speaker					Edition -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[APS2714S-R](#)