

### Product Description

Glass fibre-reinforced for maximum mechanical stability; Supporting surface for spanner means scratches on the housing are avoided



### Application range

- For locking SKINTOP® cable glands in boreholes without thread.

### Benefits

- Glass fibre-reinforced for maximum mechanical stability
- Supporting surface for spanner means scratches on the housing are avoided

### Design

- Metric connection thread acc. to EN 50262

### Approvals

- UL File Nr. E79903

### Note

- UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
- Designed for use with metric SKINTOP® plastic cable glands

## Technical Data

### Upon request

Available without collar (without surface for assembling tool)

### Colour delivered

Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant

### Material

Polyamide, glass fibre-reinforced

### Temperature range

Fixed: -40°C to +100°C

Dynamic: -20°C to +100°C

## Article List

| Part number                   | Article designation / size | SW (mm) | Pieces / PU |
|-------------------------------|----------------------------|---------|-------------|
| SKINTOP® GMP-GL-M silver grey |                            |         |             |
| 53119000                      | 12 x 1,5                   | 17      | 100         |
| 53119010                      | 16 x 1,5                   | 22      | 100         |
| 53119020                      | 20 x 1,5                   | 27      | 100         |
| 53119030                      | 25 x 1,5                   | 34      | 100         |
| 53119040                      | 32 x 1,5                   | 41      | 100         |
| 53119050                      | 40 x 1,5                   | 50      | 25          |
| 53119060                      | 50 x 1,5                   | 60      | 25          |
| 53119070                      | 63 x 1,5                   | 75      | 25          |
| SKINTOP® GMP-GL-M black       |                            |         |             |
| 53119100                      | 12 x 1,5                   | 17      | 100         |
| 53119110                      | 16 x 1,5                   | 22      | 100         |
| 53119120                      | 20 x 1,5                   | 27      | 100         |
| 53119130                      | 25 x 1,5                   | 34      | 100         |
| 53119140                      | 32 x 1,5                   | 41      | 100         |
| 53119150                      | 40 x 1,5                   | 50      | 25          |
| 53119160                      | 50 x 1,5                   | 60      | 25          |
| 53119170                      | 63 x 1,5                   | 75      | 25          |
| SKINTOP® GMP-GL-M light grey  |                            |         |             |
| 53119003                      | 12 x 1,5                   | 17      | 100         |
| 53119013                      | 16 x 1,5                   | 22      | 100         |
| 53119023                      | 20 x 1,5                   | 27      | 100         |
| 53119033                      | 25 x 1,5                   | 34      | 100         |
| 53119043                      | 32 x 1,5                   | 41      | 100         |
| 53119053                      | 40 x 1,5                   | 50      | 25          |



|          |          |    |    |
|----------|----------|----|----|
| 53119063 | 50 x 1,5 | 60 | 25 |
| 53119073 | 63 x 1,5 | 75 | 25 |

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.