




- SMD Package •
- 3000 Vrms Isolation with reinforced insulation •
- Operating Temperature Range : -40°C to +85°C •


Electrical Parameters @ 25° C

Primary Inductance (μ H Min.)	Leakage Inductance (μ H Max.)	Interwinding Capacitance (pF Max.)	Turns Ratio ($\pm$ 5%)	Primary DCR (Ω Max.)
250	.15	5	1:1	.35

Schematic



Package



Dimensions

Dim.	(Inches)			(millimeters)		
	Min.	Max.	Nom.	Min.	Max.	Nom.
A	.280	.300	.290	7.11	7.62	7.37
B	.280	.300	.290	7.11	7.62	7.37
C	.230	.250	.240	5.84	6.35	6.10
D	---	---	.200	---	---	5.08
E	.010	.015	.012	.254	.381	.318
F	---	---	.100	---	---	2.54
G	.380	.400	.390	9.65	10.1	9.91
H	.018	.022	.020	.457	6	.508
I	.008	.012	.010	.203	.559	.254
J	---	---	.085	---	.305	2.16
K	0°	8°	---	0°	---	---
L	.035	.055	.045	.889	8°	1.14
M	---	---	.030	---	1.40	.762
N	---	---	.100	---	---	2.54
P	---	---	.085	---	---	2.16
Q	---	---	.450	---	---	11.43