




LOC	DIST	REVISIONS				
FT	64	TR	LTR	DESCRIPTION	DATE	DWN
		L		REV PER 063C-0104-01	04SEP01	RB

D


C

B

A




RECOMMENDED MOUNTING HOLE PATTERN



SECTION A-A

ROTATED 90° CW
SCALE 10:1
FOR -6, -7 & -8 ONLY

1. RECEPTACLE ACCEPTS AN .008-.014 THK. I.C. LEAD.
2. TWO .000030 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TUBE LOADED.



SECTION A-A

ROTATED 90° CW
SCALE 10:1
FOR -1, -2, -3 & 2--3 ONLY

SUPSD BY 643649-2	△	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-643649-3
		TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-8
	OBSOLETE	△	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-7
	OBSOLETE	TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-6
		△	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-4
	OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-3
	OBSOLETE	△	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-2
		TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	643649-1
		CONTACT FINISH	CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. CYRUS 6-1-84	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK N. JONES 7-3-84	NAME J. GRAY 7-10-84	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1066	SOCKET ASSY, SIP, 17 POS, DIPLOMATE DL	
MATERIAL SEE TABLE		APPLICATION SPEC 114-1049	SIZE A1	
FINISH SEE TABLE		WEIGHT -	CAGE CODE 00779	
		CUSTOMER DRAWING		SCALE 5:1
		SHEET 1 OF 1		REV L

D

C

B

A