

North American Region

Download Instructions and Warranty Information

[English](#) | [Français](#) | [Español](#)



Product Detail:

Designation: Duo Charger

Color: Black and Green, Blue or Magenta

Capabilities: 1 to 2 "AA" NOTE: When charging a single battery, use bay (1) only
1 to 2 "AAA"

Charging Current: Quick Charge 1-2 "AA-AAA" 550mA
Slow Charge 1-2 "AA-AAA" 125mA

Trickle Charge: 20-60mA

Shutoff Mechanism: Delta V, Max Voltage and Timer Control

Delta V Detection 10mV per cell

Max Voltage 1.65V per cell

Max Timer Control Quick Charge "AA" 5.5 hours

Quick Charge "AAA" 1.5 hours

Slow Charge "AA" No Timer

Slow Charge "AAA" 10 hours

Charger Input : Quick Charge DC 5V 500mA

Slow Charge DC 5V 100mA

AC Adapter Input: 100-240V AC 50/60Hz 150mA

AC Adapter Output: DC 5V, 500mA

Weight (charger): 68 grams (2.4 oz.)

Dimensions (mm): 33 x 101 x 40 (H x L x W)

Safety Features: Delta V Charging Cut Off

Max Voltage Shutoff

Reverse Polarity Protection

Primary Battery Detection

VERSATILE

- Charges through the USB & wall outlet



FAST

- Charges
2 AAA in 1.6 Hours
(900 mAh)
2 AA in 4.5 Hours
(2500 mAh)



FUN

- 3 Fun colors available
Green
Blue
Magenta



Duo Charger



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.