


Number of contacts


9–50




Turned solder pins, straight

Identification	No. of contacts	Part No.
Performance levels Explanations see page 05.04 Other performance levels on request		Performance level 3 Performance level 2
Male connector metal shell with dimples	9 15 25 37 50	09 67 009 5654 09 67 015 5654 09 67 025 5654 09 67 037 5654 09 67 050 5654 ¹⁾
Female connector metal shell	9 15 25 37 50	09 67 009 4754 09 67 015 4754 09 67 025 4754 09 67 037 4754 09 67 050 4754 ¹⁾


Male connector



Female connector



Board drillings



	a	b _{±0.1}	c	g	h
9	30.9	25.0	12.5	4 x [2.74] = [10.96]	3 x [2.74] = [8.22]
15	39.2	33.3	12.5	7 x [2.74] = [19.18]	6 x [2.74] = [16.44]
25	53.1	47.0	12.5	12 x [2.76] = [33.12]	11 x [2.76] = [30.36]
37	69.4	63.5	12.5	18 x [2.76] = [49.68]	17 x [2.76] = [46.92]
50	67.0	61.1	15.4	16 x [2.76] = [44.16]	15 x [2.76] = [41.40]

Dimensions in mm

¹⁾ Not normally kept in stock

Mating conditions see page 05.04