






VIEW "A"



NOTES

1. MATERIAL & COLOR : SEE TABLE
2. MATCHED HOUSING : 35180-040*
35180-060*
3. APPLICABLE TERMINAL : 35746-0*10
4. APPLICABLE T.P.A : 35182-019*



NO	PRODUCT		MATERIAL	
	PART NO	MATERIAL NO	COLOR	DESCRIPTION
1	35181-0200	351810200	NATURAL	PBT
2	35181-0204	351810204	BLUE	(UL94V-0)
3	35181-0209	351810209	NATURAL	PBT/PC(UL94V-0)

REVISED	EC NO: KOR2008-0048	2007/09/10
DRWN: JHPARK01	2007/09/10	
CHKD: WY. YANG	2007/09/10	
APPR: YUNSIKKIM	2007/09/10	
REV	DESCRIPTION	

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± 0.3	± ---
ANGULAR ± 1 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
JS. KANG	
CHECKED BY	DATE
APPROVED BY	DATE
MATERIAL NO.	
SIZE	SEE TABLE
A3	

SCALE	3:1
DESIGN UNITS	METRIC
THIRD ANGLE PROJECTION	
TITLE	
.070 MULTI W/W CONN FEMALE HSG-2P(A)	
MOLEX INCORPORATED	
DOCUMENT NO.	SD-35181-020*
SHEET NO.	1 OF 01