

BS,C ,201995,002

B

GEN. ST.

01

02

03

04

05

06

07

08

0D

50

60

70

80

90

INT. ST.

10

11

12

13

14

18

20

31

32

33

34

38

39

40

42

43

44

45

46

48

56

70

72

73

75

76

81

82

83

84

88

REV.

DATE

DESCRIPTION

BY

C'K'D'

A

2003-01-21

CONVERSION REVISION 0E

KN

B

2006-08-03


106-0119

VIVEK




BKP

POS. 1


25



NOTE 3



PART NR.	L1	L2
HM2H**P16	3.0	25.4
HM2H**P1096	3.9	26.3
HM2H**P1116	4.1	26.5
HM2H**P1156	4.5	26.9
HM2H**P1196	4.9	27.3



NOTES :

- MATERIAL: HOUSING : GLASSREINFORCED POLYESTER UL94-V0
SPRING CONTACTS : COPPER ALLOY
- PLATING : 2.5 - 6.4 μ SnPb (90/10) OVER 1.2 - 3.8 μ Ni.
- LOCATIONS OF SLOTS TO BE DEFINED BY CUSTOMER. AS EXAMPLE THE SHROUD TYPE HM2H26P1--6 IS DRAWN WITH DISCRIMINATION - POLARISATION SLOTS IN POSITIONS 2, 10, 14 AND 24.

1DEC ±0,2 2DEC ±0,1 ANGLES ±1°	APPR. DRAFT CHECKED	DATE 1995-09-07	SIGN. G.Droesbeke	MRV SHROUD 50 MM / SHIELDED
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PROD. MGR. PR.ENG. MGR. PR. MGT. MGR.			CAT. No. HM2H**P1--6
ALL DIMENSIONS IN MM				FCI www.fciconnect.com
				SCALE 2.5/1
				BS,C ,201995,002
				DRAWING No. CUSTOMER DRAWING
				REVISION

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY. NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NIET NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS TERUGZENDING VERPLICHT.

REFERENCES



PDM: Rev:B

STATUS: Released

Printed: Dec -02, 2007