


| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
|                                                |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |





#### Material

- Contact pin: Brass
- Surface of solder tail: Tin plated
- Flange screw nut: Brass M2.5
- Insulator (housing): Thermoplastic (UL94V-0)

#### Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:

RoHS Compliant



PART NUMBER:


OSTVKXX3250

No. of Poles  
02: 2 Poles  
:  
24: 24 Poles

COLOR  
0: Black  
5: Green (Standard)  
6: Blue  
8: Grey

N=Number of poles

#### P.C.B LAYOUT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



| TITLE                 |                      | OSTVK - 3.81mm Series with flange 45° 2p-24p |                      |                 |             |            |
|-----------------------|----------------------|----------------------------------------------|----------------------|-----------------|-------------|------------|
| PART NO.              | OSTVKXX3250          | DWG NO.                                      |                      | OSTVKXX3250.DWG |             |            |
| APPROVED              | CHECKED              | DESIGNED                                     | DRAWN                | CUST NO.        | Tolerance   |            |
| Shi Jun<br>2006.10.23 | Marvin<br>2006.10.23 | Marvin<br>2006.10.23                         | Marvin<br>2006.10.23 |                 | UNIT: mm    | X. ±0.50   |
|                       |                      |                                              |                      |                 | SCALE: NONE | X.X ±0.30  |
|                       |                      |                                              |                      |                 |             | X.XX ±0.10 |
|                       |                      |                                              |                      |                 |             | X° ±1°     |
|                       |                      |                                              |                      | SHEET: 01/01    | REV: D      |            |