





## OPTICAL PATCH CABLE AND ADAPTOR

| FOPC | END 1                                                        | END 2                                                        | CABLE LENGTH                                                                                                                                | FIBERS          | CONSTRUCTION                                                                                                                                                                                                                                                   |
|------|--------------------------------------------------------------|--------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|      | <b>-01</b><br>= MTP® Male<br><br><b>-02</b><br>= MTP® Female | <b>-01</b><br>= MTP® Male<br><br><b>-02</b><br>= MTP® Female | <b>-003</b><br>= 3 Meters<br><br><b>-010</b><br>= 10 Meters<br><br><b>-100</b><br>= 100 Meters<br>(Other lengths available as custom parts) | <b>-12, -24</b> | <b>-01</b><br>= 3 mm Round Jacket<br><br><br><b>12 FIBER</b><br><br><br><b>24 FIBER</b> |






  
**FOPC-01-01-XXX-12-01**  
  
  
**FOPC-02-02-XXX-24-01**

**SPECIFICATIONS**  
**Compliant Specifications:**  
 TIA-604-5-D (FOCIS 5)  
 TIA-568-C.3  
 IEC-61754-7-1

View complete specifications at: [samtec.com?FOPC](http://samtec.com?FOPC)

| OPA | PORTS                                              | KEY                                                  | FLANGE              |
|-----|----------------------------------------------------|------------------------------------------------------|---------------------|
|     | <b>-S</b><br>= Single<br><br><b>-D</b><br>= Double | <b>-1</b><br>= Opposed<br><br><b>-2</b><br>= Aligned | <b>-F</b><br>= Full |



  
**-S**  
  
  
**-D**

**SPECIFICATIONS**  
**Compliant Specifications:**  
 TIA-604-5-D (FOCIS 5)  
 IEC-61754-7  
**Recommended Panel Thickness:**  
 (1.75 mm) .069"  
 (The OPA can be installed with any panel thickness but mounting hardware is needed for any thickness that is not (1.75 mm) .069".  
 Contact the Optics Group at [FireFly@samtec.com](mailto:FireFly@samtec.com) for questions about panel thickness and mounting hardware.)

View complete specifications at: [samtec.com?OPA](http://samtec.com?OPA)

**Notes:**  
 MTP® is a registered trademark of US ConneC Ltd.  
  
 Some lengths, styles and options are non-standard, non-returnable