



Specifications:

Current rating:2.0A AC/DC

Voltage rating:250V AC/DC

Contact resistance:20m ohm max.

Withstanding Voltage:500V AC/minute

Insulation resistance:1000M ohm min.

Temperature Rating:-40°C ~ +105°C

Materials:

Insulator:PBT UL94V-0

Insulator Color:Black


Contact:Copper Alloy

Plating:Gold Plated

How To Order

2208S-14X-E10

Emtry No. Of 8 Pin
G:Gold Plated
T:Tin Plated
No. Of Positions
Straight Type



PCB Layout

RoHS Compliant

F				DRAWN: Blake Huang	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	繼德工業股份有限公司 <i>Neltron Industrial Co., Ltd.</i>	
E							
D				CHECKED: Jerry Chen	UNIT: MM	DESCRIPTION: 2.0mm Pin Header Double Rows Straight Type	SIZE A4
C					SCALE: 1:1		
B				APPROVAL: Mike Wu	SHEET: 1 / 1	PART NO: 2208S-14X-E10	
A	18-May-2016	(PC0001)	Blake Huang				
REV	DATE	FILE	BY		PROJECTION: 		