

Note that, for some of the types shown here, order might be unable to be received by the MISUMI Thailand, Malaysia, Indonesia, and/or India offices.


Shim Rings

Standard

Standard



Standard	Material	Hardness	Thickness (T) Tolerance								
			0.01	0.02	0.03	0.05	0.1	0.2	0.3	0.5	1.0
CIMRS	SUS304H	370~430HV	±0.003		±0.005	±0.02	±0.03	±0.035	±0.04	±0.05	
CIMRB	Brass (C2801P or C2680P)	-	-	-	-	±0.005	±0.02	±0.03	±0.04	±0.05	±0.08
CIMR	SPCC Equivalent	-	-	-	-	-	±0.03	±0.04	±0.06	±0.11	



✓ (✓)

SUS304H

No specification available for plate thickness (T) without value.

Part Number		D Selection	T Selection	Unit Price				
Type	d			CIMRS				
				T0.01, 0.05	T0.02, 0.03	T0.1-0.3	T0.5	T1.0
CIMRS	2	3	0.01 0.02 0.03 0.05 0.1 0.2 0.3 0.5 1.0				-	-
		4 5 6					-	-
	3	4					-	-
		5 6 7 8 9 10					-	-
	4	5					-	-
		6 7 8 9 10 12 13						
	5	7 8 9 10 12 13 14 15 16						
	6	8 9 10 12 13 14 15 16 18						
	8	10 12 13 14 15 16 18 20						
	10	12 13 14 15 16 18 20						
	12	15 16 18 20 21 22						
	15	18 20 21 22 24						
	16	20 21 22 24 28						
	17	20 21 22 24 28 30 32						
	20	24 28 30 32 35 40						
	22	28 30 32 35 40						
	25	30 32 35 40 42						
	28	32 35 40 42 45						
	30	35 40 42 45 50						
	35	42 45 50 55						
	40	45 50 55						
	45	50 55						

Brass, SPCC

Part Number		D Selection	T Selection	Unit Price						
Type	d			CIMRB			CIMR			
				T0.05	T0.1-0.3	T0.5	T1.0	T0.1-0.3	T0.5	T1.0
CIMRB CIMR	2	4 5 6	(0.05) For CIMRB only 0.1 0.2 0.3 0.5 1.0							
	3	5 6 7 8 10								
	4	6 7 8 10 12								
	5	7 8 10 12 14 16								
	6	8 10 12 14 16								
	8	12 14 16 18 20								
	10	12 14 16 18 20								
	12	16 18 20 21 22								
	15	18 20 21 22 24								
	16	20 21 22 24 28								
	17	20 21 22 24 28 30 32								
	20	24 28 30 32 35 40								
	22	28 30 32 35 40								
	25	30 32 35 40 42								
	28	32 35 40 42 45								
	30	35 40 42 45 50								
	35	42 45 50 55								
	40	45 50 55								
	45	50 55								

Ordering Example

Part Number - D - T

CIMRS5 - 12 - 0.1