



**APC Symmetra PX 20kW Scalable to 40kW N+1, 400V
uninterruptible power supply (UPS) 20 kVA 20000 W**

Brand : APC

Product code: SY20K40H

Product name : Symmetra PX 20kW Scalable to 40kW
N+1, 400V

Symmetra PX 20kW Scalable to 40kW N+1, 400V
APC Symmetra PX 20kW Scalable to 40kW N+1, 400V. Output power capacity: 20 kVA, Output power: 20000 W. Typical backup time at full load: 3.8 min, Typical backup time at half load: 14.4 min, Replacement battery cartridge: RBC Quantity - 1. Product colour: Black. Bundled software: Web/SNMP Management Card. Interface: Contact Closure, RJ-45 10 Base-T ethernet for web/ SNMP/ Telnet management, SmartSlot, Output connections: (1)Hard Wire 5-wire (3PH + N + G) (1)Screw Terminals , Input connection type: Hard Wire 5-wire (3PH + N + G)



Features		Operational conditions			
Output power capacity *	20 kVA	Operating relative humidity (H-H)	0 - 95%		
Output power *	20000 W	Storage relative humidity (H-H)	0 - 95%		
Emergency Power Off (EPO)	✓	Operating altitude	0 - 3000 m		
Battery		Packaging data			
Typical backup time at full load	3.8 min	Bundled software	Web/SNMP Management Card		
Typical backup time at half load	14.4 min	Other features			
Replacement battery cartridge	RBC Quantity - 1				
Design					
Product colour *	Black			I/O ports	Contact Closure, RJ-45 10 Base-T ethernet for web/ SNMP/ Telnet management, SmartSlot Available Smart Slot Interface Quantity - 2 Pre-Installed SmartSlot Cards - AP9617
Operational conditions					
Operating temperature (T-T)	0 - 40 °C	Interface	Contact Closure, RJ-45 10 Base-T ethernet for web/ SNMP/ Telnet management, SmartSlot		
Storage temperature (T-T)	-50 - 40 °C				
		Output connections	(1)Hard Wire 5-wire (3PH + N + G) (1)Screw Terminals		
		Input connection type	Hard Wire 5-wire (3PH + N + G)		
		Dimensions (WxDxH)	610 x 900 x 2080 mm		
		Output voltage note	Configurable for 380: 400 or 415 V 3 Phase nominal output voltage		
		Networking features	✓		

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.