




Pos.4

Pos.1

1

3

5

4

2

25±5

L⁺⁰₋₅₀

TYCO P/N
T/D YYWW
MADE IN CHINA

LABEL

(25)

(13)

(35)

PIN ASSIGNMENT :

USB A

2

3

1

4

Shell

Pair 1

White(D-)

Green(D+)

Red(Vbus)

Black(Gnd)

Drain Braid

NC

NC

NC

NC

NC

NOTES:

1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.

2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.

3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.

4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 2700MM PER USB SPECIFICATIONS.

5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

-

DWN
BOVEY LIU

CHK

APVD
F.D. McCORKEL

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

25/FEB/02

15/MAR/02

-

-

-

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

CABLE ASSEMBLY, USB A TYPE TO NC

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1487601

RESTRICTED TO

-

SCALE
N.T.S

SHEET
1 OF 1

REV
C

PART NO.

1487601-1

1487601-2

LENGTH(L)

2000

1500

AR	AR	MR	COPPER FOIL, W: 5MM	5
1	1	PC	LABEL, 25x35mm, White 25x13mm	4
AR	AR	KG	Overmold PVC, 40P, Color: Black(BK01)	3
AR	AR	MR	USB 2.0 Cable 28AWG*1P+24AWG*2C+Al/Mylar +Drain+Braid, Color: Black(BK01).	2
1	1	EA	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 A Type.	1
-2	-1	U/M	DESCRIPTION	ITEM

AMP 1470-19 REV 31MAR2000