



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	23.0	± max
T:	9.0	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	4.0	± max
B:	9.20	± nom
C:	6.90	± nom



Electrical Specifications

Resistance:	75.0 Ω	± 25 %
Max Steady State Current upto 65°C:	4.00	A
Max Rec. Energy Rating:	240	J
Actual Failure Instantaneous Energy:	430	J
Maximum Capacitance @ 120 VAC:	16,400	μ f
Maximum Capacitance @ 240 VAC:	4,167	μ f
Maximum Capacitance @ 440 VAC:	963	μ f
Maximum Capacitance @ 680 VAC:	480	μ f
Resistance @ 100% Max Current:	0.41	Ω
Resistance @ 50% Max Current:	0.90	Ω
Body Temperature at 100% Max Current:	169.00	°c
Dissipation Constant:	51.8	mw/°c
Thermal Time Constant:	122	Sec.
Material Type (for Beta and Curve):		

MS22 75004

Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 3111 N. Deer Run Road Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: a

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[MS22 75004](#)