



MCG / MCGF  
Metal Grommet




Specifications:

- Material: 304 Stainless Steel, coated with black nylon 11 & a cushion of TPE 60 Shore D UL94V-0 rating
- Temperature Rating: -40°F (-40°C) to 285°F (140°C)
- The MCGF is the more flexible of the two due to the design

Features:

- Dielectric Strength: 1000 volts @ 60Hz
- Locks onto panel with finger pressure
- Sold in 100 foot reels that can be cut to length using metal shears Item No. MCGS-1



| Item No. |          | Approval | Fits Panel Thickness |           | Width W |     | Color Coded | Roll Length |
|----------|----------|----------|----------------------|-----------|---------|-----|-------------|-------------|
| Figure 1 | Figure 2 |          | In                   | mm        | In      | mm  |             |             |
| MCG-1N   | —        | ✓        | 0.029 - 0.045        | 0.7 - 1.1 | 0.140   | 3.6 | —           | 30          |
| MCG-2N   | —        | ✓        | 0.044 - 0.056        | 1.1 - 1.4 | 0.140   | 3.6 | —           | 30          |
| MCG-3N   | —        | ✓        | 0.055 - 0.069        | 1.4 - 1.7 | 0.140   | 3.6 | —           | 30          |
| MCG-4N   | —        | ✓        | 0.069 - 0.090        | 1.7 - 2.3 | 0.180   | 4.6 | —           | 30          |
| MCG-6N   | —        | ✓        | 0.113 - 0.130        | 2.9 - 3.3 | 0.180   | 4.6 | —           | 30          |
| —        | MCGF-1N  | ✓        | 0.029 - 0.045        | 0.7 - 1.1 | 0.130   | 3.3 | White       | 30          |
| —        | MCGF-2N  | ✓        | 0.044 - 0.056        | 1.1 - 1.4 | 0.130   | 3.3 | Pink        | 30          |
| —        | MCGF-3N  | ✓        | 0.055 - 0.069        | 1.4 - 1.7 | 0.130   | 3.3 | Yellow      | 30          |

NGSG / SNGSG / PGSG / SPGSG  
Continuous Grommet Edging with Adhesive




Specifications:

- Material Options:  
UL94 HB Nylon Temperature Rating: -40°F (-40°C) to 248°F (120°C)  
PE: Temperature Rating: -40°F (-40°C) to 149°F (65°C)
- Color: See Table

Features:

- Adhesive provides self-retaining grip eliminating the need for epoxy
- Sizes 6, 7, and 8 are extra flexible
- Solid version is for straight edges
- Serrated version for round, square, and rectangular holes
- Polyethylene material is very flexible



| Solid Profile Item No. |           | Serrated Profile Item No. |            | Material      | Panel Thickness Range |           | A Ref. |     | B Ref. |     | C Ref. |     | Roll Length |
|------------------------|-----------|---------------------------|------------|---------------|-----------------------|-----------|--------|-----|--------|-----|--------|-----|-------------|
| Natural                | Black     | Natural                   | Black      |               | In                    | mm        | In     | mm  | In     | mm  | In     | mm  |             |
| NGSG-2                 | —         | SNGSG-2                   | SNGSG-2B   | UL94 HB Nylon | 0.037 - 0.071         | 0.9 - 1.8 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| NGSG-2.5               | —         | SNGSG-2.5                 | —          | UL94 HB Nylon | 0.072 - 0.105         | 1.8 - 2.7 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| NGSG-3                 | —         | SNGSG-3                   | —          | UL94 HB Nylon | 0.106 - 0.164         | 2.7 - 4.2 | 0.188  | 4.8 | 0.047  | 1.2 | 0.156  | 4.0 | 30          |
| PGSG-2                 | PGSG-2B   | SPGSG-2                   | SPGSG-2B   | Polyethylene  | 0.037 - 0.071         | 0.9 - 1.8 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| PGSG-6                 | PGSG-6B   | SPGSG-6                   | —          | Polyethylene  | 0.037 - 0.071         | 0.9 - 1.8 | 0.160  | 4.1 | 0.025  | 0.6 | 0.060  | 1.5 | 30          |
| PGSG-2.5               | PGSG-2.5B | SPGSG-2.5                 | SPGSG-2.5B | Polyethylene  | 0.072 - 0.105         | 1.8 - 2.7 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| —                      | —         | SPGSG-7                   | —          | Polyethylene  | 0.072 - 0.105         | 1.8 - 2.7 | 0.188  | 4.8 | 0.035  | 0.9 | 0.100  | 2.5 | 30          |
| PGSG-3                 | PGSG-3B   | SPGSG-3                   | SPGSG-3B   | Polyethylene  | 0.106 - 0.164         | 2.7 - 4.2 | 0.188  | 4.8 | 0.047  | 1.2 | 0.156  | 4.0 | 30          |
| —                      | —         | SPGSG-8                   | —          | Polyethylene  | 0.106 - 0.164         | 2.7 - 4.2 | 0.188  | 4.8 | 0.035  | 0.9 | 0.156  | 4.0 | 30          |

NGS / PGS / SNGS / SPGS  
Continuous Grommet Edging




Specifications:

- Material: See Table
- Color: See Table

Features:

- Solid version is for straight edges
- Serrated version for round, square, and rectangular holes
- Polyethylene material is very flexible



| Solid Profile Item No. |          | Serrated Profile Item No. |           | Material      | Panel Thickness Range |           | A Ref. |     | B Ref. |     | C Ref. |     | Roll Length |
|------------------------|----------|---------------------------|-----------|---------------|-----------------------|-----------|--------|-----|--------|-----|--------|-----|-------------|
| Natural                | Black    | Natural                   | Black     |               | In                    | mm        | In     | mm  | In     | mm  | In     | mm  |             |
| NGS-1                  | —        | SNGS-1                    | SNGS-1B   | UL94 HB Nylon | 0.026-0.036           | 0.7 - 0.9 | 0.125  | 3.2 | 0.031  | 0.8 | 0.031  | 0.8 | 30          |
| NGS-2                  | —        | SNGS-2                    | SNGS-2B   | UL94 HB Nylon | 0.037-0.071           | 0.9 - 1.8 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| —                      | —        | SNGS-2.5                  | SNGS-2.5B | UL94 HB Nylon | 0.072-0.105           | 1.8 - 2.7 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| —                      | —        | SNGS-3                    | SNGS-3B   | UL94 HB Nylon | 0.106-0.164           | 2.7 - 4.2 | 0.188  | 4.8 | 0.047  | 1.2 | 0.156  | 4.0 | 30          |
| —                      | —        | SNGS-4                    | SNGS-4B   | UL94 HB Nylon | 0.164-0.187           | 4.2 - 4.7 | 0.188  | 4.8 | 0.047  | 1.2 | 0.188  | 4.8 | 30          |
| —                      | —        | SNGS-5                    | —         | UL94 HB Nylon | 0.188-0.250           | 4.8 - 6.4 | 0.188  | 4.8 | 0.047  | 1.2 | 0.250  | 6.4 | 30          |
| PGS-1                  | PGS-1B   | SPGS-1                    | —         | Polyethylene  | 0.026-0.036           | 0.7 - 0.9 | 0.125  | 3.2 | 0.031  | 0.8 | 0.031  | 0.8 | 30          |
| PGS-2                  | —        | SPGS-2                    | —         | Polyethylene  | 0.037-0.071           | 0.9 - 1.8 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| PGS-2.5                | PGS-2.5B | SPGS-2.5                  | SPGS-2.5B | Polyethylene  | 0.072-0.105           | 1.8 - 2.7 | 0.172  | 4.4 | 0.031  | 0.8 | 0.109  | 2.8 | 30          |
| PGS-3                  | —        | SPGS-3                    | —         | Polyethylene  | 0.106-0.164           | 2.7 - 4.2 | 0.188  | 4.8 | 0.047  | 1.2 | 0.156  | 4.0 | 30          |