







- Unique compliant tail pins conform to $1,02 \pm 0,07$ finished hole diameter without stressing inner layers.
- Two tail lengths are offered for 1,52 - 2,54 and 2,29 - 3,3 thick panels.
- Uses M-M# 4612 or 4613 pins with #30 contact rated at 3 amps. See page 131 for pin details.



APPLICATION OF COMPLIANT TAIL PINS

Mill-Max' patented* compliant tail features precision machined pins that are hollow and slotted to conform to a $1,02 \pm 0,07$ diameter PTH. As the pin is inserted, the slot compresses to fit the PTH, thus avoiding damage (see illustration at left). The pin's tail has fine serrations that form a perfect "gas tight" connection that doesn't require soldering. And since the pin doesn't damage the hole, compliant tail sockets and connectors can be easily replaced.

*Patent No. 4,799,904.

Total number of pins				Quantity per tube	Ordering Information							
					L=3,05mm (for 1,52 - 2,54 thick panel)	L=4,45mm (for 2,29 - 3,3 thick panel)	For RoHS compliance, select  plating code. For the all gold option (XX=13) also change part number from 146-XX-XXX-41-01XQ00 to 146-13-XXX-41-01X100 					
	A	B	C									
6	7,6	7,62	10,1	67	146-XX-306-41-012000	146-XX-306-41-013000	For RoHS compliance, select  plating code. For the all gold option (XX=13) also change part number from 146-XX-XXX-41-01XQ00 to 146-13-XXX-41-01X100 					
8	10,1	7,62	10,1	50	146-XX-308-41-012000	146-XX-308-41-013000						
14	17,7	7,62	10,1	28	146-XX-314-41-012000	146-XX-314-41-013000						
16	20,3	7,62	10,1	25	146-XX-316-41-012000	146-XX-316-41-013000						
18	22,8	7,62	10,1	22	146-XX-318-41-012000	146-XX-318-41-013000						
20	25,3	7,62	10,1	20	146-XX-320-41-012000	146-XX-320-41-013000						
24	30,4	7,62	10,1	16	146-XX-324-41-012000	146-XX-324-41-013000						
22	27,8	10,16	12,7	18	146-XX-422-41-012000	146-XX-422-41-013000						
24	30,5	15,24	17,7	16	146-XX-624-41-012000	146-XX-624-41-013000						
28	35,5	15,24	17,7	14	146-XX-628-41-012000	146-XX-628-41-013000						
32	40,6	15,24	17,7	12	146-XX-632-41-012000	146-XX-632-41-013000						
40	50,8	15,24	17,7	10	146-XX-640-41-012000	146-XX-640-41-013000						
SPECIFY PLATING CODE XX=				13 		93			99		43 	44 
Sleeve (Pin) 				0,25µm Au		5,08µm Sn/Pb			5,08µm Sn/Pb		5,08µm Sn	5,08µm Sn
Contact (Clip) 				0,76µm Au		0,76µm Au			5,08µm Sn/Pb		0,76µm Au	5,08µm Sn