

200 V - 1,000 V Single Phase Bridge


12.0 A Forward Current

70 ns - 3000 ns Recovery Time

1402 - 1410

1402F - 1410F

1402UF - 1410UF





ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage (V _{rw})	Average Rectified Current @TC (I _o)		Reverse Current @ V _{rw} m (I _r)		Forward Voltage (V _f)		1 Cycle Surge Current t _p =8.3ms (I _{fsm})	Repetitive Surge Current (I _{frm})	Reverse Recovery Time (1) (T _{rr})	Thermal Impd. θ _{J-C}
		55°C	100°C	25°C	100°C	25°C		25°C	25°C	25°C	
	Volts	Amps	Amps	μA	μA	Volts	Amps	Amps	Amps	ns	°C/W
1402	200	12.0	9.0	1.0	25	1.1	3.0	150	25	3000	3.2
1406	600	12.0	9.0	1.0	25	1.1	3.0	150	25	3000	3.2
1410	1000	12.0	9.0	1.0	25	1.1	3.0	150	25	3000	3.2
1402F	200	12.0	9.0	1.0	25	1.2	3.0	100	20	150	3.2
1406F	600	12.0	9.0	1.0	25	1.5	3.0	100	20	150	3.2
1410F	1000	12.0	9.0	1.0	25	1.5	3.0	100	20	150	3.2
1402UF	200	12.0	9.0	1.0	25	1.7	3.0	100	20	70	3.2
1406UF	600	12.0	9.0	1.0	25	1.7	3.0	100	20	70	3.2
1410UF	1000	12.0	9.0	1.0	25	1.7	3.0	100	20	70	3.2

(1)T_{rr} Testing: I_f=0.5A, I_r=1.0A, I_{rr}=0.25A *Op. Temp. & Stg. Temp. = -55°C to +150°C Isolation Voltage: 1500V

10



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

1402 - 1410 • 1402F - 1410F • 1402UF - 1410UF

