


PATENTED

J-Pro™ Cable Support System

- Patented design provides complete horizontal and vertical 1" bend radius control that helps prevent degradation of cable performance
- UL 2043 and CAN/ULC S102.2 listed and suitable for use in air handling spaces
- Pre-riveted assemblies allow for attachment to walls, ceilings, beams, threaded rods, drop wires and underfloor supports to meet requirements of a variety of applications
- Wide cable support base prevents pinch points that could cause damage to cables
- Cable tie channel allows user to easily install 3/4" (19.1mm) Tak-Ty® Cable Ties to retain cable bundle
- Durable non-metallic J Hook materials provide the ability to manage and support a large number of cables
- Material: Black Nylon 6.6 J Hook with metal attachments


JP2W-L20

JP2WP2-L20

JP2CM-L20

JP2DW-L20

Part Number	Part Description	Max. Bundle Capacity		Max. Cable Capacity			Std. Pkg. Qty.
		In.	mm	Cat 6A (0.300")	Cat 6 (0.240")	Cat 5e (0.225")	

Wall Mount

JP75W-L20	J Hook for wall mount applications. One 1/4" (M6) mounting hole for user supplied screw. Not for use with powder actuated fasteners.	0.75	19.0	5	8	10	50
JP131W-L20		1.31	33.3	15	25	29	50
JP2W-L20		2.00	50.8	30	46	55	50
JP4W-X20		4.00	101.6	115	180	200	10

Wall Mount with Bracket

JP75WP2-L20	J Hook for powder actuated installation on walls. One 5/32" (M4) mounting hole and one 1/4" (M6) mounting hole for user supplied fasteners.	0.75	19.0	5	8	10	50
JP131WP2-L20		1.31	33.3	15	25	29	50
JP2WP2-L20		2.00	50.8	30	46	55	50
JP4WP2-X20		4.00	101.6	115	180	200	10

Ceiling Mount

JP75CM-L20	J Hook with ceiling mount bracket that has one 3/16" (M5), 1/4" (M6), and 3/8" (M10) mounting hole.	0.75	19.0	5	8	10	50
JP131CM-L20		1.31	33.3	15	25	29	50
JP2CM-L20		2.00	50.8	30	46	55	50
JP4CM-X20		4.00	101.6	115	180	200	10

Drop Wire and Threaded Rod Clip

JP75DW-L20	J Hook with clip for use with #12 wire, threaded rod up to 3/8" (9.5mm) in diameter.	0.75	19.0	5	8	10	50
JP131DW-L20		1.31	33.3	15	25	29	50
JP2DW-L20		2.00	50.8	30	46	55	50

Suitable for use in air handling spaces in accordance with Sec. 300-22(c) and (d) of the National Electrical Code. JP4 family of parts suitable for use in single unit configurations. Listed in accordance with CAN/ULC S102.2 when mounted as single units or in pairs. Minimum spacing of 4 feet (1220mm) required between mount points. (Flame spread rating = 0, Smoke developed classification = 30). All dimensions represent typical outer cable diameter in inches (mm).



J-Pro™ Cable Support System (continued)



JP2SBC50-L20



JP2SBC50R-L20



JP2SBC87-L20



JP2SBC87R-L20



JP2HBC25R-L20

JP2HBC50R-L20

JP2HBC75R-L20

Part Number	Part Description	Max. Bundle Capacity		Max. Cable Capacity			Std. Pkg. Qty.
		In.	mm	Cat 6A (0.300")	Cat 6 (0.240")	Cat 5e (0.225")	
Screw-On Beam Clamps							
JP75SBC50-L20	J Hook with screw-on beam clamp for use with flanges up to 1/2" (12.7mm) thick. Non-rotating mount.	0.75	19.0	5	8	10	50
JP131SBC50-L20		1.31	33.3	15	25	29	50
JP2SBC50-L20		2.00	50.8	30	46	55	50
JP4SBC50-X20		4.00	101.6	115	180	200	10
JP75SBC50R-L20	J Hook with screw-on beam clamp for use with flanges up to 1/2" (12.7mm) thick. Rotates 360 degrees.	0.75	19.0	5	8	10	50
JP131SBC50R-L20		1.31	33.3	15	25	29	50
JP2SBC50R-L20		2.00	50.8	30	46	55	50
JP4SBC50R-X20		4.00	101.6	115	180	200	10
JP75SBC87-L20	J Hook with screw-on beam clamp for use with flanges up to 3/4" (19.1mm) thick. Non-rotating mount.	0.75	19.0	5	8	10	50
JP131SBC87-L20		1.31	33.3	15	25	29	50
JP2SBC87-L20		2.00	50.8	30	46	55	50
JP4SBC87-X20		4.00	101.6	115	180	200	10
JP75SBC87R-L20	J Hook with screw-on beam clamp for use with flanges up to 3/4" (19.1mm) thick. Rotates 360 degrees.	0.75	19.0	5	8	10	50
JP131SBC87R-L20		1.31	33.3	15	25	29	50
JP2SBC87R-L20		2.00	50.8	30	46	55	50
JP4SBC87R-X20		4.00	101.6	115	180	200	10
Hammer-On Beam Clamps							
JP75HBC25R-L20	J Hook with hammer-on beam clamp for use with flanges 1/8" – 1/4" (3.2mm – 6.4mm) thick. Rotates 360 degrees.	0.75	19.0	5	8	10	50
JP131HBC25R-L20		1.31	33.3	15	25	29	50
JP2HBC25R-L20		2.00	50.8	30	46	55	50
JP4HBC25R-X20		4.00	101.6	115	180	200	10
JP75HBC50R-L20	J Hook with hammer-on beam clamp for use with flanges 5/16" – 1/2" (7.9mm – 12.7mm) thick. Rotates 360 degrees.	0.75	19.0	5	8	10	50
JP131HBC50R-L20		1.31	33.3	15	25	29	50
JP2HBC50R-L20		2.00	50.8	30	46	55	50
JP4HBC50R-X20		4.00	101.6	115	180	200	10
JP75HBC75R-L20	J Hook with hammer-on beam clamp for use with flanges 9/16" – 3/4" (14.3mm – 19.1mm) thick. Rotates 360 degrees.	0.75	19.0	5	8	10	50
JP131HBC75R-L20		1.31	33.3	15	25	29	50
JP2HBC75R-L20		2.00	50.8	30	46	55	50
JP4HBC75R-X20		4.00	101.6	115	180	200	10

Suitable for use in air handling spaces in accordance with Sec. 300-22(c) and (d) of the National Electrical Code. JP4 family of parts suitable for use in single unit configurations. Listed in accordance with CAN/ULC S102.2 when mounted as single units or in pairs. Minimum spacing of 4 feet (1220mm) required between mount points. (Flame spread rating = 0, Smoke developed classification = 30). All dimensions represent typical outer cable diameter in inches (mm).

Table continues on page L.68



J-Pro™ Cable Support System (continued)



JP2ZP-L20



JP2CP-L20



JP2UF100-L20

Part Number	Part Description	Max. Bundle Capacity		Max. Cable Capacity			Std. Pkg. Qty.
		In.	mm	Cat 6A (0.300")	Cat 6 (0.240")	Cat 5e (0.225")	
Z-Purlin Clips							
JP75ZP-L20	J Hook with z-purlin clip for use with angled flanges up to 1/4" (6.4mm) thick.	0.75	19.0	5	8	10	50
JP131ZP-L20		1.31	33.3	15	25	29	50
JP2ZP-L20		2.00	50.8	30	46	55	50
JP4ZP-X20		4.00	101.6	115	180	200	10
C-Purlin Clips							
JP75CP-L20	J Hook with c-purlin clip for use with vertical flanges up to 1/4" (6.4mm) thick.	0.75	19.0	5	8	10	50
JP131CP-L20		1.31	33.3	15	25	29	50
JP2CP-L20		2.00	50.8	30	46	55	50
JP4CP-X20		4.00	101.6	115	180	200	10
Underfloor Pedestal Support Clamp							
JP75UF100-L20	J Hook with underfloor clamp for use with pedestal support 7/8" square or 1 1/8" – 1 3/8" in diameter.	0.75	19.0	5	8	10	50
JP131UF100-L20		1.31	33.3	15	25	29	50
JP2UF100-L20		2.00	50.8	30	46	55	50
JP4UF100-X20		4.00	101.6	115	180	200	10

Suitable for use in air handling spaces in accordance with Sec. 300-22(c) and (d) of the National Electrical Code. JP4 family of parts suitable for use in single unit configurations. Listed in accordance with CAN/ULC S102.2 when mounted as single units or in pairs. Minimum spacing of 4 feet (1220mm) required between mount points. (Flame spread rating = 0, Smoke developed classification = 30). All dimensions represent typical outer cable diameter in inches (mm).