




2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.
3. SUGGESTED PANEL OPENING DIMENSIONS. SEE APPLICATION SPEC. 114-2154 FOR PANEL THICKNESS AND POSITION RECOMMENDATIONS
4. SUGGESTED CLEARANCE BETWEEN TOP OF CONNECTOR AND TOP PANEL OPENING
5. PACKAGED: POCKET TAPE & REEL (PER EIA 481 SPECIFICATIONS)


POCKET TAPE WIDTH - 44mm
POCKET PITCH - 24mm
POCKET DEPTH - 16.7mm

CLEAR COVER TAPE, PSA
CLEAR COVER TAPE TRAILER - 1220mm, WRAPPED ON REEL HUB

PLASTIC REEL - 381mm DIAMETER

PRODUCT QUANTITY - 200 PIECES PER REEL

- | | |
|---|---|
| 6 | ZERO INSERTION FORCE POST WITH RECOMMENDED PCB LAYOUT |
| 7 | DATUM ESTABLISHED BY CUSTOMER. |
| 8 | CONNECTOR SHOULD BE POSITIONED THRU PANEL CUTOUT AS SHOWN TO SUPPORT TOP OF MODULAR JACK FOR STRAIN RELIEF |
| 9 | MANUFACTURING DATE CODE LOCATED APPROXIMATELY AS SHOWN
FIRST 2 DIGITS ARE YEAR, SECOND 2 DIGITS ARE WORK WEEK
LAST DIGIT IS THE DAY OF THE WEEK |



DETAIL Z
SCALE 20:1



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09MA2005 D. Willis / D. MAYER CHG 09MA2005 APPROVED W. WESMAN 09MA2005 S. FLECKINGER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P L C ± 1 P L C ± 2 P L C ±0.25 3 P L C ± 4 P L C ± ANGLES ± FINISH		NAME INVERTED MOD JACK ASSEMBLY, IXI, SHIELDED SURFACE MOUNT, 8 POSITION RJ45	
		PRODUCT SPEC 108-1163-7 APPLICATION SPEC 114-6040/114-2154 WEIGHT -		SIZE A1	
MATERIAL SEE NOTE 1		CAGE CODE 00779		DRAWING NO C-6339160	
SEE NOTE 1		COUNTRY OF ORIGIN CHINA		RESTRICTED TO NO	
COUNTRY OF ORIGIN CHINA		CUSTOMER DRAWING NO		SCALE 8:1	
SHEET 1		OF 1		REV D	