

REV. D

| DIMENSIONS ARE IN INCHES  |                        |       | UNLESS OTHERWISE NOTED | TOLERANCES ARE: |  | TITLE:                       | DWG NO:      |
|---------------------------|------------------------|-------|------------------------|-----------------|--|------------------------------|--------------|
| ONE PLACE DECIMALS ±      | THREE PLACE DECIMALS ± | .005  | ANGLES                 | ± 2°            |  | LEAD SOCKET<br>CARRIER STRIP | SCS-1XX-X-X  |
| TWO PLACE DECIMALS ± .010 | FOUR PLACE DECIMALS ±  | .0020 |                        |                 |  |                              |              |
|                           |                        |       |                        |                 |  |                              | SHEET 1 OF 1 |

SCS-1XX-X-XX


NO. OF POSITIONS  
-01 THRU -50LEAD STYLE  
SPECIFY LEAD STYLE  
FROM TABLE 1

PLATING

- G: GOLD CONTACT, GOLD SHELL  
(SPECIFY -GG IN SOCKET SUFFIX -XX)
- T: GOLD CONTACT, TIN SHELL  
(SPECIFY -GT IN SOCKET SUFFIX -XX)
- S: LOW GOLD CONTACT, TIN SHELL  
(SPECIFY -ST IN SOCKET SUFFIX -XX)
- TT: TIN CONTACT, TIN SHELL  
(SPECIFY -TT IN SOCKET SUFFIX -XX)

TABLE 1

| STYLE | LEAD<br>SOCKET |
|-------|----------------|
| -1A   | SC-1W1-XX-2    |
| -1B   | SC-1W1-XX-1    |
| -1C   | SC-1W1-XX-3    |
| -2    | SC-1P1-XX      |
| -3    | SC-1S1-XX      |
| -4    | SC-2S1-XX      |
| -5A   | SC-2P1-XX      |
| -7    | SC-1P3-XX      |
| -8    | SC-2P3-XX      |
| -9    | SC-2P2-XX      |
| -10   | SC-3P1-XX      |
| -11   | SC-4P1-XX      |
| -12   | SC-5P1-XX      |
| -14   | SC-1M1-XX      |
| -15   | SC-1M2-XX      |
| -18   | SC-6P1-XX      |
| -19   | SC-8P1-XX      |
| -21A  | EZ-1W1-XX-2    |
| -21B  | EZ-1W1-XX-1    |
| -21C  | EZ-1W1-XX-3    |
| -22   | EZ-1P1-XX      |
| -23   | EZ-1S1-XX      |
| -28   | EZ-2P3-XX      |
| -29   | EZ-2P2-XX      |
| -30   | EZ-3P1-XX      |
| -31   | EZ-4P1-XX      |
| -32   | EZ-5P1-XX      |
| -34   | EZ-1M1-XX      |
| -35   | EZ-1M2-XX      |
| -38   | EZ-6P1-XX      |
| -39   | EZ-8P1-XX      |
| -41   | SP-101-XX      |



## NOTE:

1. CARRIER (T-1SS2) TO BE FULLY INSERTED INTO LEAD SOCKETS. INSERTION DEPTH WILL VARY FOR THE DIFFERENT LEAD STYLES.

Do not scale  
from this print

## PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION  
CONFIDENTIAL AND PROPRIETARY TO  
SAMTEC INC. AND SHALL NOT BE  
REPRODUCED OR TRANSMITTED IN  
ANY FORM OR BY ANY MEANS  
ELECTRONIC, MECHANICAL, OR  
OTHERWISE OR USED FOR ANY PURPOSE  
OTHER THAN THAT FOR WHICH IT WAS  
OBTAINED WITHOUT THE EXPRESSED  
WRITTEN CONSENT OF SAMTEC INC.

PLOT SCALE 1 = .166

## MATERIAL:

T-1SS2  
BRASS, 1/2 HARD

## LEAD SOCKET

SHELL: BRASS 1/2 HARD  
CONTACT: BeCu, ALLOY 172H

**samtec**MISC\MKTG  
SCS-MKT

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150  
PHONE (812) 944-6733 P.O. BOX 1147  
CODE 55322

MADE BY: TY 7-28-82

SCS-1XX-X-X

SHEET 1 OF 1