



TS9013

500mA CMOS Low Dropout Voltage Regulator

SOT-89



SOT-223



Pin assignment

SOT-89

1. Gnd
2. Input
3. Output

SOT-223

1. Input
2. Gnd
3. Output

Low Power Consumption 2uA(typ)
Low Drop Out Voltage 0.6V

General Description

The TS9013 series is a positive voltage regulator developed utilizing CMOS technology featured very low power consumption, low dropout voltage and high output voltage accuracy. Built in low on-resistor provides low dropout voltage and large output current. A 1uF or greater can be used as an output capacitor.

The TS9013 series are prevented device failure under the worst operation condition with both thermal shutdown and current fold-back. These series are recommended for configuring portable devices and large current application, respectively.

This series are offered in 3-pin SOT-89 and SOT-223 package.


Features

- ✧ Dropout voltage typically 0.4V @Io=500mA (Vo=5V)
- ✧ Output current up to 500mA
- ✧ Low power consumption, 2uA(typ) @Vo=5V
- ✧ Output voltage +/-2%
- ✧ Internal current limit
- ✧ Thermal shutdown protection

Applications

- ✧ Palmtops
- ✧ Video recorders
- ✧ Battery powered equipment
- ✧ PC peripherals
- ✧ CD-ROM, DVD ROM
- ✧ Digital signal camera

Block Diagram




Ordering Information

Part No.	Operating Temp. (Ambient)	Package
TS9013 $\underline{x}$ CW	-20 ~ +85 °C	SOT-223
TS9013 $\underline{x}$ CY		SOT-89

Note: Where $\underline{x}$ denotes voltage option, available are A=1.5V, D=1.8V, K=2.5V, S=3.3V, 5=5.0V. Contact factory for additional voltage options.

Typical Application Circuit






Absolute Maximum Rating							
Input Supply Voltage		Vin(max.)	+12		V		
Input Operating Voltage		Vin(opr. Typ.)	+10				
Output Current		Io	PD / (Vin – Vo)		V		
Power Dissipation (without heat sink)	SOT-89	PD	0.55		W		
	SOT-223		0.625				
Thermal Resistance	SOT-89	Rθja	180		°C/W		
	SOT-223		160				
Thermal Resistance	SOT-89	Rθjc	18		°C/W		
	SOT-223		15				
Operating Junction Temperature Range		Tj	-40 ~ +125		°C		
Storage Temperature Range		TSTG	-65 ~ +150		°C		
Lead Soldering Temperature (260 °C)			10		S		
Caution: Stress above the listed absolute rating may cause permanent damage to the device.							
Electrical Characteristics							
Ta = 25 °C unless otherwise specified.							
Parameter		Conditions		Min	Typ	Max	Unit
Output Voltage	Vin=Vo + 1V, Io =10mA,	TS90135	4.900	5.0	5.100	V	
		TS9013S	3.234	3.3	3.366		
		TS9013K	2.450	2.5	2.550		
		TS9013D	1.764	1.8	1.836		
		TS9013A	1.47	1.5	1.575		
Maximum Output Current	Vin=Vo+1V,		500	--	--	mA	
Input Stability	Vo+1V ≤ Vin ≤ Vo+2V, Io=1mA		--	0.2	0.3	%	
Load Regulation (Note1)	Vin=Vo+1V, 1mA≤IL≤500mA	TS90135	--	40	80	mV	
		TS9013S					
	Vin=Vo+1V, 1mA≤IL≤400mA	TS9013K	--	40	90		
		TS9013D					
		TS9013A					
Dropout Voltage (Note 2)	Io=500mA	TS90135	--	600	750	mV	
		TS9013S	--	600	750		
	Io=400mA	TS9013K	--	600	850		
		TS9013D	--	600	850		
		TS9013A	--	850	1100		
Quiescent Current	Vin=Vo+1V, Io=0A		--	2	5	uA	
Output Current Limit	Vout < 0.4V		--	550	--	mA	
Power Supply Rejection Ratio	At f=100KHz, Io=10mA,		--	30	--	dB	
Output Voltage Temperature Coefficient (Note 3)			--	100	--	ppm/°C	

Note: 1. Regulation is measured at constant junction temperature, using pulsed ON time.

2. Dropout is measured at constant junction temperature, using pulsed ON time, and the criterion is Vout inside target value +/-2%.


3. Guaranteed by design.

SOT-89 Mechanical Drawing



SOT-89 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.40	4.60	0.173	0.181
B	1.50	1.7	0.059	0.070
C	2.30	2.60	0.090	0.102
D	0.40	0.52	0.016	0.020
E	1.50	1.50	0.059	0.059
F	3.00	3.00	0.118	0.118
G	0.89	1.20	0.035	0.047
H	4.05	4.25	0.159	0.167
I	1.4	1.6	0.055	0.068
J	0.35	0.44	0.014	0.017

SOT-223 Mechanical Drawing



SOT-223 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	6.350	6.850	0.250	0.270
B	2.900	3.100	0.114	0.122
C	3.450	3.750	0.136	0.148
D	0.595	0.635	0.023	0.025
E	4.550	4.650	0.179	0.183
F	2.250	2.350	0.088	0.093
G	0.835	1.035	0.032	0.041
H	6.700	7.300	0.263	0.287
I	0.250	0.355	0.010	0.014
J	10°	16°	10°	16°
K	1.550	1.800	0.061	0.071