74AUP2G14

Low-power dual Schmitt trigger inverter

Rev. 5 — 4 December 2012 Product data sheet

1. General description

The 74AUP2G14 provides two inverting buffers with Schmitt trigger action which accept standard input signals. They are capable of transforming slowly changing input signals into sharply defined, jitter-free output signals.

This device ensures a very low static and dynamic power consumption across the entire V_{CC} range from 0.8 V to 3.6 V.

This device is fully specified for partial power-down applications using I_{OFF}. The I_{OFF} circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

The inputs switch at different points for positive and negative-going signals. The difference between the positive voltage V_{T+} and the negative voltage V_{T-} is defined as the input hysteresis voltage V_H.

2. Features and benefits

- Wide supply voltage range from 0.8 V to 3.6 V
- High noise immunity
- ESD protection:
  - HBM JESD22-A114F Class 3A exceeds 5000 V
  - MM JESD22-A115-A exceeds 200 V
  - CDM JESD22-C101E exceeds 1000 V
- Low static power consumption; I_{CC} = 0.9 μA (maximum)
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Inputs accept voltages up to 3.6 V
- Low noise overshoot and undershoot < 10 % of V_{CC}
- I_{OFF} circuitry provides partial Power-down mode operation
- Multiple package options
- Specified from –40 °C to +85 °C and –40 °C to +125 °C

3. Applications

- Wave and pulse shaper
- Astable multivibrator
- Monostable multivibrator

4. Ordering information

Table 1. Ordering information

Type number	Package			
	Temperature range	Name	Description	Version
74AUP2G14GW	–40 °C to +125 °C	SC-88	plastic surface-mounted package; 6 leads	SOT363
74AUP2G14GM	–40 °C to +125 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 × 1.45 × 0.5 mm	SOT886
74AUP2G14GF	–40 °C to +125 °C	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 × 1 × 0.5 mm	SOT891
74AUP2G14GN	–40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 0.9 × 1.0 × 0.35 mm	SOT1115
74AUP2G14GS	–40 °C to +125 °C	XSON6	extremely thin small outline package; no leads; 6 terminals; body 1.0 × 1.0 × 0.35 mm	SOT1202

5. Marking

Table 2. Marking

Type number	Marking code[1]
74AUP2G14GW	pK
74AUP2G14GM	pK
74AUP2G14GF	pK
74AUP2G14GN	pK
74AUP2G14GS	pK

[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

6. Functional diagram



Fig 1. Logic symbol



Fig 2. IEC logic symbol



Fig 3. Logic diagram

7. Pinning information

7.1 Pinning



Fig 4. Pin configuration SOT363



Fig 5. Pin configuration SOT886



Fig 6. Pin configuration SOT891, SOT1115 and SOT1202

7.2 Pin description

Table 3. Pin description

Symbol	Pin	Description
1A	1	data input
GND	2	ground (0 V)
2A	3	data input
2Y	4	data output
V_{CC}	5	supply voltage
1Y	6	data output

8. Functional description

Table 4. Function table[1]

Input	Output
nA	**nY**
L	H
H	L

[1] H = HIGH voltage level; L = LOW voltage level.

9. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V_{CC}	supply voltage			–0.5	+4.6	V
I_{IK}	input clamping current	$V_I < 0$ V		–50	-	mA
V_I	input voltage		[1]	–0.5	+4.6	V
I_{OK}	output clamping current	$V_O < 0$ V		–50	-	mA
V_O	output voltage	Active mode and Power-down mode	[1]	–0.5	+4.6	V
I_O	output current	$V_O = 0$ V to V_{CC}		-	±20	mA
I_{CC}	supply current			-	50	mA
I_{GND}	ground current			–50	-	mA
T_{stg}	storage temperature			–65	+150	°C
P_{tot}	total power dissipation	T_{amb} = –40 °C to +125 °C	[2]	-	250	mW

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For SC-88 packages: above 87.5 °C the value of P_{tot} derates linearly with 4.0 mW/K.
For XSON6 packages: above 118 °C the value of P_{tot} derates linearly with 7.8 mW/K.

10. Recommended operating conditions

Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V_{CC}	supply voltage		0.8	3.6	V
V_I	input voltage		0	3.6	V
V_O	output voltage	Active mode	0	V_{CC}	V
		Power-down mode; V_{CC} = 0 V	0	3.6	V
T_{amb}	ambient temperature		–40	+125	°C

11. Static characteristics

Table 7. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
T_{amb} = 25 °C						
V_{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = –20 μA; V_{CC} = 0.8 V to 3.6 V	V_{CC} – 0.1	-	-	V
		I_O = –1.1 mA; V_{CC} = 1.1 V	0.75 × V_{CC}	-	-	V
		I_O = –1.7 mA; V_{CC} = 1.4 V	1.11	-	-	V
		I_O = –1.9 mA; V_{CC} = 1.65 V	1.32	-	-	V
		I_O = –2.3 mA; V_{CC} = 2.3 V	2.05	-	-	V
		I_O = –3.1 mA; V_{CC} = 2.3 V	1.9	-	-	V
		I_O = –2.7 mA; V_{CC} = 3.0 V	2.72	-	-	V
		I_O = –4.0 mA; V_{CC} = 3.0 V	2.6	-	-	V

Table 7. Static characteristics *...continued*
At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = 20 μA; V_{CC} = 0.8 V to 3.6 V	-	-	0.1	V
		I_O = 1.1 mA; V_{CC} = 1.1 V	-	-	0.3 × V_{CC}	V
		I_O = 1.7 mA; V_{CC} = 1.4 V	-	-	0.31	V
		I_O = 1.9 mA; V_{CC} = 1.65 V	-	-	0.31	V
		I_O = 2.3 mA; V_{CC} = 2.3 V	-	-	0.31	V
		I_O = 3.1 mA; V_{CC} = 2.3 V	-	-	0.44	V
		I_O = 2.7 mA; V_{CC} = 3.0 V	-	-	0.31	V
		I_O = 4.0 mA; V_{CC} = 3.0 V	-	-	0.44	V
I_I	input leakage current	V_I = GND to 3.6 V; V_{CC} = 0 V to 3.6 V	-	-	±0.1	μA
I_{OFF}	power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±0.2	μA
ΔI_{OFF}	additional power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V to 0.2 V	-	-	±0.2	μA
I_{CC}	supply current	V_I = GND or V_{CC}; I_O = 0 A; V_{CC} = 0.8 V to 3.6 V	-	-	0.5	μA
ΔI_{CC}	additional supply current	$V_I = V_{CC} - 0.6$ V; I_O = 0 A; V_{CC} = 3.3 V	-	-	40	μA
C_I	input capacitance	V_I = GND or V_{CC}; V_{CC} = 0 V to 3.6 V	-	1.1	-	pF
C_O	output capacitance	V_O = GND; V_{CC} = 0 V	-	1.7	-	pF
T_{amb} = –40 °C to +85 °C						
V_{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = –20 μA; V_{CC} = 0.8 V to 3.6 V	$V_{CC} - 0.1$	-	-	V
		I_O = –1.1 mA; V_{CC} = 1.1 V	0.7 × V_{CC}	-	-	V
		I_O = –1.7 mA; V_{CC} = 1.4 V	1.03	-	-	V
		I_O = –1.9 mA; V_{CC} = 1.65 V	1.30	-	-	V
		I_O = –2.3 mA; V_{CC} = 2.3 V	1.97	-	-	V
		I_O = –3.1 mA; V_{CC} = 2.3 V	1.85	-	-	V
		I_O = –2.7 mA; V_{CC} = 3.0 V	2.67	-	-	V
		I_O = –4.0 mA; V_{CC} = 3.0 V	2.55	-	-	V
V_{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = 20 μA; V_{CC} = 0.8 V to 3.6 V	-	-	0.1	V
		I_O = 1.1 mA; V_{CC} = 1.1 V	-	-	0.3 × V_{CC}	V
		I_O = 1.7 mA; V_{CC} = 1.4 V	-	-	0.37	V
		I_O = 1.9 mA; V_{CC} = 1.65 V	-	-	0.35	V
		I_O = 2.3 mA; V_{CC} = 2.3 V	-	-	0.33	V
		I_O = 3.1 mA; V_{CC} = 2.3 V	-	-	0.45	V
		I_O = 2.7 mA; V_{CC} = 3.0 V	-	-	0.33	V
		I_O = 4.0 mA; V_{CC} = 3.0 V	-	-	0.45	V
I_I	input leakage current	V_I = GND to 3.6 V; V_{CC} = 0 V to 3.6 V	-	-	±0.5	μA
I_{OFF}	power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±0.5	μA

Table 7. Static characteristics *...continued*
At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
ΔI_{OFF}	additional power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V to 0.2 V	-	-	±0.6	μA
I_{CC}	supply current	V_I = GND or V_{CC}; I_O = 0 A; V_{CC} = 0.8 V to 3.6 V	-	-	0.9	μA
ΔI_{CC}	additional supply current	$V_I = V_{CC} - 0.6$ V; I_O = 0 A; V_{CC} = 3.3 V	-	-	50	μA
T_{amb} = –40 °C to +125 °C						
V_{OH}	HIGH-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = –20 μA; V_{CC} = 0.8 V to 3.6 V	$V_{CC} - 0.11$	-	-	V
		I_O = –1.1 mA; V_{CC} = 1.1 V	$0.6 \times V_{CC}$	-	-	V
		I_O = –1.7 mA; V_{CC} = 1.4 V	0.93	-	-	V
		I_O = –1.9 mA; V_{CC} = 1.65 V	1.17	-	-	V
		I_O = –2.3 mA; V_{CC} = 2.3 V	1.77	-	-	V
		I_O = –3.1 mA; V_{CC} = 2.3 V	1.67	-	-	V
		I_O = –2.7 mA; V_{CC} = 3.0 V	2.40	-	-	V
		I_O = –4.0 mA; V_{CC} = 3.0 V	2.30	-	-	V
V_{OL}	LOW-level output voltage	$V_I = V_{T+}$ or V_{T-}				
		I_O = 20 μA; V_{CC} = 0.8 V to 3.6 V	-	-	0.11	V
		I_O = 1.1 mA; V_{CC} = 1.1 V	-	-	$0.33 \times V_{CC}$	V
		I_O = 1.7 mA; V_{CC} = 1.4 V	-	-	0.41	V
		I_O = 1.9 mA; V_{CC} = 1.65 V	-	-	0.39	V
		I_O = 2.3 mA; V_{CC} = 2.3 V	-	-	0.36	V
		I_O = 3.1 mA; V_{CC} = 2.3 V	-	-	0.50	V
		I_O = 2.7 mA; V_{CC} = 3.0 V	-	-	0.36	V
		I_O = 4.0 mA; V_{CC} = 3.0 V	-	-	0.50	V
I_I	input leakage current	V_I = GND to 3.6 V; V_{CC} = 0 V to 3.6 V	-	-	±0.75	μA
I_{OFF}	power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V	-	-	±0.75	μA
ΔI_{OFF}	additional power-off leakage current	V_I or V_O = 0 V to 3.6 V; V_{CC} = 0 V to 0.2 V	-	-	±0.75	μA
I_{CC}	supply current	V_I = GND or V_{CC}; I_O = 0 A; V_{CC} = 0.8 V to 3.6 V	-	-	1.4	μA
ΔI_{CC}	additional supply current	$V_I = V_{CC} - 0.6$ V; I_O = 0 A; V_{CC} = 3.3 V	-	-	75	μA

12. Dynamic characteristics

Table 8. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 8.

Symbol	Parameter	Conditions		25 °C			−40 °C to +125 °C			Unit
				Min	Typ[1]	Max	Min	Max (85 °C)	Max (125 °C)	
C_L = 5 pF										
t_{pd}	propagation delay	nA to nY; see Figure 7	[2]							
		V_{CC} = 0.8 V		-	19.9	-	-	-	-	ns
		V_{CC} = 1.1 V to 1.3 V		2.7	5.9	11.0	2.4	11.1	11.2	ns
		V_{CC} = 1.4 V to 1.6 V		2.6	4.3	6.6	2.4	7.1	7.4	ns
		V_{CC} = 1.65 V to 1.95 V		2.1	3.7	5.4	2.0	6.0	6.2	ns
		V_{CC} = 2.3 V to 2.7 V		2.0	3.0	4.1	1.7	4.5	4.7	ns
		V_{CC} = 3.0 V to 3.6 V		1.9	2.8	3.6	1.5	3.9	4.0	ns
C_L = 10 pF										
t_{pd}	propagation delay	nA to nY; see Figure 7	[2]							
		V_{CC} = 0.8 V		-	23.4	-	-	-	-	ns
		V_{CC} = 1.1 V to 1.3 V		2.9	6.8	12.7	2.8	12.8	12.9	ns
		V_{CC} = 1.4 V to 1.6 V		2.8	5.0	7.7	2.6	8.2	8.6	ns
		V_{CC} = 1.65 V to 1.95 V		2.7	4.2	6.2	2.5	6.7	7.1	ns
		V_{CC} = 2.3 V to 2.7 V		2.3	3.6	4.8	2.1	5.2	5.5	ns
		V_{CC} = 3.0 V to 3.6 V		2.1	3.3	4.3	2.0	4.5	4.7	ns
C_L = 15 pF										
t_{pd}	propagation delay	nA to nY; see Figure 7	[2]							
		V_{CC} = 0.8 V		-	26.9	-	-	-	-	ns
		V_{CC} = 1.1 V to 1.3 V		3.3	7.6	14.3	3.0	14.5	14.7	ns
		V_{CC} = 1.4 V to 1.6 V		3.3	5.5	8.6	2.9	9.4	9.8	ns
		V_{CC} = 1.65 V to 1.95 V		2.8	4.7	7.0	2.8	7.7	8.1	ns
		V_{CC} = 2.3 V to 2.7 V		2.7	4.0	5.5	2.4	5.9	6.2	ns
		V_{CC} = 3.0 V to 3.6 V		2.6	3.8	4.8	2.2	5.2	5.4	ns
C_L = 30 pF										
t_{pd}	propagation delay	nA to nY; see Figure 7	[2]							
		V_{CC} = 0.8 V		-	37.3	-	-	-	-	ns
		V_{CC} = 1.1 V to 1.3 V		4.0	9.8	18.7	3.9	19.6	20.0	ns
		V_{CC} = 1.4 V to 1.6 V		3.7	7.1	11.2	3.8	12.3	12.9	ns
		V_{CC} = 1.65 V to 1.95 V		3.6	6.0	9.1	3.6	10.0	10.6	ns
		V_{CC} = 2.3 V to 2.7 V		3.5	5.2	6.9	3.2	7.5	7.9	ns
		V_{CC} = 3.0 V to 3.6 V		3.3	4.8	6.1	3.1	7.1	7.4	ns

Table 8. Dynamic characteristics *...continued*
Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 8.

Symbol	Parameter	Conditions	25 °C			−40 °C to +125 °C			Unit
			Min	Typ[1]	Max	Min	Max (85 °C)	Max (125 °C)	
C_L = 5 pF, 10 pF, 15 pF and 30 pF									
C_{PD}	power dissipation capacitance	f_i = 1 MHz; V_I = GND to V_{CC} [3][4]							
		V_{CC} = 0.8 V	-	2.6	-	-	-	-	pF
		V_{CC} = 1.1 V to 1.3 V	-	2.7	-	-	-	-	pF
		V_{CC} = 1.4 V to 1.6 V	-	2.9	-	-	-	-	pF
		V_{CC} = 1.65 V to 1.95 V	-	3.1	-	-	-	-	pF
		V_{CC} = 2.3 V to 2.7 V	-	3.7	-	-	-	-	pF
		V_{CC} = 3.0 V to 3.6 V	-	4.3	-	-	-	-	pF

[1] All typical values are measured at nominal V_{CC}.

[2] t_{pd} is the same as t_{PLH} and t_{PHL}.

[3] All specified values are the average typical values over all stated loads.

[4] C_{PD} is used to determine the dynamic power dissipation (P_D in μW).
$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma(C_L \times V_{CC}^2 \times f_o)$ where:
f_i = input frequency in MHz;
f_o = output frequency in MHz;
C_L = load capacitance in pF;
V_{CC} = supply voltage in V;
N = number of inputs switching;
$\Sigma(C_L \times V_{CC}^2 \times f_o)$ = sum of the outputs.

13. Waveforms



Measurement points are given in Table 9.

Logic levels: V_{OL} and V_{OH} are typical output voltage levels that occur with the output load.

Fig 7. The data input (nA) to output (nY) propagation delays

Table 9. Measurement points

Supply voltage	Output	Input		
V_{CC}	V_M	V_M	V_I	$t_r = t_f$
0.8 V to 3.6 V	0.5 × V_{CC}	0.5 × V_{CC}	V_{CC}	≤ 3.0 ns



Test data is given in Table 10.

Definitions for test circuit:

R_L = Load resistance.

C_L = Load capacitance including jig and probe capacitance.

R_T = Termination resistance should be equal to the output impedance Z_o of the pulse generator.

V_{EXT} = External voltage for measuring switching times.

Fig 8. Test circuit for measuring switching times

Table 10. Test data

Supply voltage	Load		V_{EXT}		
V_{CC}	C_L	R_L [1]	t_{PLH}, t_{PHL}	t_{PZH}, t_{PHZ}	t_{PZL}, t_{PLZ}
0.8 V to 3.6 V	5 pF, 10 pF, 15 pF and 30 pF	5 kΩ or 1 MΩ	open	GND	2 × V_{CC}

[1] For measuring enable and disable times R_L = 5 kΩ, for measuring propagation delays, set-up and hold times and pulse width R_L = 1 MΩ.

14. Transfer characteristics

Table 11. Transfer characteristics

Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 8.

Symbol	Parameter	Conditions	25 °C			−40 °C to +125 °C			Unit
			Min	Typ	Max	Min	Max (85 °C)	Max (125 °C)	
V_{T+}	positive-going threshold voltage	see Figure 9 and Figure 10							
		V_{CC} = 0.8 V	0.30	-	0.60	0.30	0.60	0.62	V
		V_{CC} = 1.1 V	0.53	-	0.90	0.53	0.90	0.92	V
		V_{CC} = 1.4 V	0.74	-	1.11	0.74	1.11	1.13	V
		V_{CC} = 1.65 V	0.91	-	1.29	0.91	1.29	1.31	V
		V_{CC} = 2.3 V	1.37	-	1.77	1.37	1.77	1.80	V
		V_{CC} = 3.0 V	1.88	-	2.29	1.88	2.29	2.32	V
V_{T-}	negative-going threshold voltage	see Figure 9 and Figure 10							
		V_{CC} = 0.8 V	0.10	-	0.60	0.10	0.60	0.60	V
		V_{CC} = 1.1 V	0.26	-	0.65	0.26	0.65	0.65	V
		V_{CC} = 1.4 V	0.39	-	0.75	0.39	0.75	0.75	V
		V_{CC} = 1.65 V	0.47	-	0.84	0.47	0.84	0.84	V
		V_{CC} = 2.3 V	0.69	-	1.04	0.69	1.04	1.04	V
		V_{CC} = 3.0 V	0.88	-	1.24	0.88	1.24	1.24	V

Table 11. Transfer characteristics *...continued*

Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 8.

Symbol	Parameter	Conditions	25 °C			−40 °C to +125 °C			Unit
			Min	Typ	Max	Min	Max (85 °C)	Max (125 °C)	
V_H	hysteresis voltage	($V_{T+} - V_{T-}$); see Figure 9, Figure 10, Figure 11 and Figure 12							
		V_{CC} = 0.8 V	0.07	-	0.50	0.07	0.50	0.50	V
		V_{CC} = 1.1 V	0.08	-	0.46	0.08	0.46	0.46	V
		V_{CC} = 1.4 V	0.18	-	0.56	0.18	0.56	0.56	V
		V_{CC} = 1.65 V	0.27	-	0.66	0.27	0.66	0.66	V
		V_{CC} = 2.3 V	0.53	-	0.92	0.53	0.92	0.92	V
		V_{CC} = 3.0 V	0.79	-	1.31	0.79	1.31	1.31	V

15. Waveforms transfer characteristics



Fig 9. Transfer characteristic



V_{T+} and V_{T-} limits at 70 % and 20 %.

Fig 10. Definition of V_{T+}, V_{T-} and V_H



Fig 11. Typical transfer characteristics; V_{CC} = 1.8 V



Fig 12. Typical transfer characteristics; V_{CC} = 3.0 V

16. Application information

The slow input rise and fall times cause additional power dissipation, this can be calculated using the following formula:

$P_{add} = f_i \times (t_r \times \Delta I_{CC(AV)} + t_f \times \Delta I_{CC(AV)}) \times V_{CC}$ where:

P_{add} = additional power dissipation (μW);

f_i = input frequency (MHz);

t_r = rise time (ns); 10 % to 90 %;

t_f = fall time (ns); 90 % to 10 %;

$\Delta I_{CC(AV)}$ = average additional supply current (μA).

Average $\Delta I_{CC(AV)}$ differs with positive or negative input transitions, as shown in Figure 13.

An example of a relaxation circuit using the 74AUP2G14 is shown in Figure 14.



(1) Positive-going edge.

(2) Negative-going edge.

Fig 13. Average I_{CC} as a function of V_{CC}



$$f = \frac{1}{T} \approx \frac{1}{a \times RC}$$

Average values for variable a are given in Table 12.

Fig 14. Relaxation oscillator

Table 12. Variable values

Supply voltage	Variable a
1.1 V	1.28
1.5 V	1.22
1.8 V	1.24
2.8 V	1.34
3.3 V	1.45

17. Package outline

Plastic surface-mounted package; 6 leads **SOT363**



DIMENSIONS (mm are the original dimensions)

UNIT	A	A_1 max	b_p	c	D	E	e	e_1	H_E	L_p	Q	v	w	y
mm	1.1 0.8	0.1	0.30 0.20	0.25 0.10	2.2 1.8	1.35 1.15	1.3	0.65	2.2 2.0	0.45 0.15	0.25 0.15	0.2	0.2	0.1

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT363			SC-88			~~04-11-08~~ 06-03-16

Fig 15. Package outline SOT363 (SC-88)

XSON6: plastic extremely thin small outline package; no leads; 6 terminals; body 1 x 1.45 x 0.5 mm SOT886



Dimensions (mm are the original dimensions)

Unit		A(1)	A_1	b	D	E	e	e_1	L	L_1
mm	max	0.5	0.04	0.25	1.50	1.05			0.35	0.40
	nom			0.20	1.45	1.00	0.6	0.5	0.30	0.35
	min			0.17	1.40	0.95			0.27	0.32

Notes
1. Including plating thickness.
2. Can be visible in some manufacturing processes.

sot886_po

Outline version	References				European projection	Issue date
	IEC	JEDEC	JEITA			
SOT886		MO-252				~~04-07-22~~ 12-01-05

Fig 16. Package outline SOT886 (XSON6)

XSON6: plastic extremely thin small outline package; no leads; 6 terminals; body 1 x 1 x 0.5 mm **SOT891**



DIMENSIONS (mm are the original dimensions)

UNIT	A max	A_1 max	b	D	E	e	e_1	L	L_1
mm	0.5	0.04	0.20 0.12	1.05 0.95	1.05 0.95	0.55	0.35	0.35 0.27	0.40 0.32

Note

1. Can be visible in some manufacturing processes.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT891						~~05-04-06~~ 07-05-15

Fig 17. Package outline SOT891 (XSON6)

**XSON6: extremely thin small outline package; no leads;
6 terminals; body 0.9 x 1.0 x 0.35 mm**

SOT1115



Dimensions

Unit		A(1)	A1	b	D	E	e	e1	L	L1
	max	0.35	0.04	0.20	0.95	1.05			0.35	0.40
mm	nom			0.15	0.90	1.00	0.55	0.3	0.30	0.35
	min			0.12	0.85	0.95			0.27	0.32

Note
1. Including plating thickness.
2. Visible depending upon used manufacturing technology.

sot1115_po

Outline version	References				European projection	Issue date
	IEC	JEDEC	JEITA			
SOT1115						~~10-04-02~~ 10-04-07

Fig 18. Package outline SOT1115 (XSON6)

XSON6: extremely thin small outline package; no leads;
6 terminals; body 1.0 x 1.0 x 0.35 mm **SOT1202**



Dimensions

Unit		A(1)	A_1	b	D	E	e	e_1	L	L_1
mm	max	0.35	0.04	0.20	1.05	1.05			0.35	0.40
	nom			0.15	1.00	1.00	0.55	0.35	0.30	0.35
	min			0.12	0.95	0.95			0.27	0.32

Note
1. Including plating thickness.
2. Visible depending upon used manufacturing technology.

sot1202_po

Outline version	References				European projection	Issue date
	IEC	JEDEC	JEITA			
SOT1202						~~10-04-02~~ 10-04-06

Fig 19. Package outline SOT1202 (XSON6)

18. Abbreviations

Table 13. Abbreviations

Acronym	Description
CDM	Charged Device Model
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model
MM	Machine Model

19. Revision history

Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74AUP2G14 v.5	20121204	Product data sheet	-	74AUP2G14 v.4
Modifications:	• Package outline drawing of SOT886 (Figure 16) modified.			
74AUP2G14 v.4	20111201	Product data sheet	-	74AUP2G14 v.3
74AUP2G14 v.3	20100722	Product data sheet	-	74AUP2G14 v.2
74AUP2G14 v.2	20090703	Product data sheet	-	74AUP2G14 v.1
74AUP2G14 v.1	20061219	Product data sheet	-	-

20. Legal information

20.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

20.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

20.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

20.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

21. Contact information

For more information, please visit: **http://www.nxp.com**

For sales office addresses, please send an email to: **salesaddresses@nxp.com**

22. Contents

For more information, please visit: http://www.nxp.com
For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 4 December 2012
Document identifier: 74AUP2G14