


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.



SPC Type No.	Wire Size (AWG)	Stud Size	L	W	E	C	T	U	Pkg QTY
CRS-ZO-0425	4	1/4" (.250)	1.34	.68	1.00	.53			10
SPC3753	4	1/4" (.250)	1.34	.68	1.00	.53			100
CRS-ZO-0437	4	3/8" (.375)	1.34	.68	1.00	.53	.280	.075	10
SPC3754	4	3/8" (.375)	1.34	.68	1.00	.53			100
CRS-ZO-0610	6	#10 (.196)	1.14	.47	.91	.52			20
SPC3750	6	#10 (.196)	1.14	.47	.91	.52			200
CRS-ZO-0625	6	1/4" (.250)	1.14	.47	.91	.52	.250		20
SPC3751	6	1/4" (.250)	1.14	.47	.91	.52			200
CRS-ZO-0631	6	5/16" (.312)	1.22	.63	.91	.52			20
SPC3752	6	5/16" (.312)	1.22	.63	.91	.52			200
CRS-ZO-0810	8	#10 (.196)	.95	.47	.72	.40			25
SPC3746	8	#10 (.196)	.95	.47	.72	.40	.050		250
CRS-ZO-0825	8	1/4" (.250)	.95	.47	.72	.40			25
SPC3747	8	1/4" (.250)	.95	.47	.72	.40	.175		250
CRS-ZO-0831	8	5/16" (.312)	1.06	.59	.77	.45			25
SPC3748	8	5/16" (.312)	1.06	.59	.77	.45			250
CRS-ZO-0837	8	3/8" (.375)	1.06	.59	.77	.45			25
SPC3749	8	3/8" (.375)	1.06	.59	.77	.45			250

REVISIONS				DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. 680			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRD
217	B	Removed Discontinued Part	DJC	6/26/97	JC	7/3/97	JC
1116	C	Add Bulk items; was CRS-ZO-*****	JWM	3/6/01	JC	3/6/01	JC

NOTES:

MATERIAL:

1. ELECTRO-TIN PLATED COPPER
2. TO BE FREE OF BURRS.
3. CAN BE CRIMPED ANYWHERE ON BARREL SURFACE.
4. VOLTAGE RATING AND TEMPERATURE RANGE:
600 V AND 347°F (175°C)
5. USE CRIMPING TOOL GROUP A: 8403-001

SPC Type No.	Wire Size (AWG)	Stud Size	L	W	E	C	T	U	Pkg QTY
CRS-ZO-1008	12 ~ 10	#8 (.174)	.68	.28	.54	.29			50
SPC3743	12 ~ 10	#8 (.174)	.68	.28	.54	.29			500
CRS-ZO-1010	12 ~ 10	#10 (.196)	.73	.38	.54	.29	.135	.040	50
SPC3744	12 ~ 10	#10 (.196)	.73	.38	.54	.29			500
CRS-ZO-1025	12 ~ 10	1/4" (.250)	.96	.54	.69	.44			50
SPC3745	12 ~ 10	1/4" (.250)	.96	.54	.69	.44			500
CRS-ZO-1406	16 ~ 14	#6 (.143)	.60	.25	.47	.22			100
SPC3739	16 ~ 14	#6 (.143)	.60	.25	.47	.22			1000
CRS-ZO-1408	16 ~ 14	#8 (.174)	.74	.31	.58	.33			100
SPC3740	16 ~ 14	#8 (.174)	.74	.31	.58	.33			1000
CRS-ZO-1410	16 ~ 14	#10 (.196)	.74	.31	.58	.33	.090		100
SPC3741	16 ~ 14	#10 (.196)	.74	.31	.58	.33			1000
CRS-ZO-1425	16 ~ 14	1/4 (.250)	.89	.47	.65	.40		.030	100
SPC3742	16 ~ 14	1/4 (.250)	.89	.47	.65	.40			1000
CRS-ZO-1806	22 ~ 18	#6 (.143)	.60	.25	.47	.22			100
SPC3737	22 ~ 18	#6 (.143)	.60	.25	.47	.22	.070		1000
CRS-ZO-1808	22 ~ 18	#8 (.174)	.74	.31	.58	.33			100
SPC3738	22 ~ 18	#8 (.174)	.74	.31	.58	.33			1000



ES8918



LR22190M6

OSHA
Acceptable

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE UNPREDICTABLE, OUR COMPANY AND THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.				DRAWING TITLE: Uninsulated Ring Terminals			
DRAWN BY: JC		DATE: 2/6/91		SIZE: A		ELECTRONIC FILE: TA-295.dwg	
CHECKED BY: JC		DATE: 11/21/91		SCALE: NTS		SHEET: 1 OF 1	
APPROVED BY: JL		DATE: 11/21/91		U.O.M.: INCHES [mm]		REV: C	