














NOTES

- 材質
ウエハー: 耐熱性ナイロン UL94V-0
ピン: 銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール: 銅合金、ニッケル下地、錫メッキ
MATERIAL
WAFFER: POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FITTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 色: ナチュラル
COLOR: NATURAL
- 嵌合相手:
ハウジング: 502351-xx00
錫メッキ端子: 50212-8*00, 50372-8*00, 560085-0101
金メッキ端子: 56161-8*81
MATES WITH
HOUSING: 502351-xx00
SN PLATING TERMINAL: 50212-8*00, 50372-8*00, 560085-0101
AU PLATING TERMINAL: 56161-8*81
- エンボス梱包品の詳細はSD-560020-002参照
DETAILED TAPING PACKAGE, SEE SD-560020-002
- ELV及びRoHS適合
ELV AND RoHS COMPLIANT
- 半田付け面のコプラナリティ: 0.1mm MAX.
CO-PLANARITY OF SOLDER TAILS TO BE 0.1mm MAX.

REVISED	EC NO.	JTR2015-0031	DRWKNAGA102	2014/10/02	CHKDHKOMATSU	2014/10/02	APPR: MAYAMOTO	2014/10/15	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
									10 UNDER	± 0.2	DRAWN BY	DATE	TITLE			
REV	DESCRIPTION	10 OVER	30 UNDER	± 0.25	30 OVER	± 0.3	ANGULAR	± 1 °	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	MATERIAL NO.	DOCUMENT NO.	SD-560020-001	SHEET NO. 1 OF 3	




2CKTS

3CKTS


4CKTS

5CKTS

6CKTS



7CKTS



REVISED	EC NO: JTR2015-0031	DRWN:KAGAI02	2014/10/02	CHKD:HKOMATSU	2014/10/02	APPR: MAYAMOTO	2014/10/15	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
										DRAWN BY SHSHIBATA	DATE 2009/02/18	TITLE 2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT molex			
										CHECKED BY HKOMATSU	DATE 2009/02/18				
										APPROVED BY AKANESHIGE	DATE 2009/02/18				
								10 UNDER		±0.2					
10 OVER 30 UNDER		±0.25													
30 OVER		±0.3													
ANGULAR ±1 °				MATERIAL NO.		DOCUMENT NO.			SHEET NO.						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE CHART		SD-560020-001			2 OF 3						
REV				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	10	9	8	7	6	5	4	3	2	1	
F	Sn										F
		11.8	15.1	19.7	22.6	560020-0800/-0820	8				
		11.8	13.1	17.7	20.6	560020-0700/-0720	7				
		11.8	12	15.7	18.6	560020-0600/-0620	6				
E		9.8	10	13.7	16.6	560020-0500/-0520	5				E
		7.8	8	11.7	14.6	560020-0400/-0420	4				
		5.8	6	9.7	12.6	560020-0300/-0320	3				
		6.3		8.0	10.9	560020-0200/-0220	2				
	PLATING	D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CKTS				
	CONNECTOR SERIES NO. 560020-**08										

		11.8	15.1	19.7	22.6	560020-0830	8				
		11.8	13.1	17.7	20.6	560020-0730	7				
		11.8	12	15.7	18.6	560020-0630	6				
		9.8	10	13.7	16.6	560020-0530	5				
		7.8	8	11.7	14.6	560020-0430	4				
		5.8	6	9.7	12.6	560020-0330	3				
		6.3		8.0	10.9	560020-0230	2				
	PLATING	D	C	B	A	EMBOSSED PACKAGE ORDER NO.	CKTS				
	CONNECTOR SERIES NO. 560020-**18										

D

C

B

A

REVISED EC NO: JTR2015-0031 DRWN:KNAGA102 2014/10/02 CHKD:HKOMATSU 2014/10/02 APPR:MAYAMOTO 2014/10/15	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY SHSHIBATA	DATE 2009/02/18	TITLE 2.0MM PITCH W/B CONN. WAFER ASSY ST. SMT			
		10 OVER 30 UNDER	± 0.25	CHECKED BY HKOMATSU	DATE 2009/02/18				
		30 OVER	± 0.3	APPROVED BY AKANESHIGE	DATE 2009/02/18	DOCUMENT NO. SD-560020-001			
		ANGULAR ±1 °		MATERIAL NO. SEE CHART					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SHEET NO. 3 OF 3			
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_J_AM_S
Rev G 2012/01/25

9

8

7

6

5

4

3

2

10

9

8

7

6


5

4


3

2


1



DETAIL Y




PULL OUT DIRECTION




NOTES


- 製品番号: 560020-***0 詳細寸法については、製品単体図面を参照ください。
PART NO. 5600020-***0 SEE SALES DRAWING FOR CONNECTOR
- 梱包数量: 650個/REEL
NUMBER OF CONNECTORS 650 PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- 材料
MATERIAL
キャリアテープ: ポリスチレン
CARRIER TAPE: POLYSTYRENE
トップテープ: PET, PE, PEF
TOP TAPE
リール: ポリスチレン
REEL: POLYSTYRENE



PULL OUT DIRECTION

DIRECTION OF CONNECTOR
IN EMBOSSED TAPEDETAIL X
(SCALE 10:1)

49.4	45.4	44	20.2	22.9	560020-0800	08
				20.9	560020-0700	07
37.4	33.4	32	14.2	18.9	560020-0600	06
				16.9	560020-0500	05
				14.9	560020-0400	04
29.4	25.4	24	11.5	12.9	560020-0300	03
				11.2	560020-0200	02
E	D	C	(B)	(A)	エンボス梱包品 製品番号 MATERIAL NO.	CIRCUITS

REVISED	EC NO: JTR2014-0066 DRWN:YAMAKI 2014/01/15 CHKD:HKOMATSU 2014/01/15 APPR:MAYAMOTO 2014/02/24	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			10 UNDER	± 0.2	DRAWN BY YTAMAKI	DATE 2012/02/29	TITLE 2.0MM PITCH W/B ST. WAFER ASSY EMBOSSED TAPE PACKAGE			
			10 OVER 30 UNDER	± 0.25	CHECKED BY HKOMATSU	DATE 2012/02/29				
			30 OVER	± 0.3	APPROVED BY MAYAMOTO	DATE 2012/03/01				
			ANGULAR ±1 °		MATERIAL NO.					DOCUMENT NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-560020-002			1 OF 1
B		REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				