

D

C

B





A

D

C

B

A



SECTION T-T

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISONS

DESCRIPTION

DATE

DWN

APVD

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—BLACK.

2

CONTACT MATERIAL: PHOSPHOR BRONZE.

3

CONTACT FINISH: .00127—.00254 [.000050—.000100] NICKEL UNDERPLATE ALL OVER; .00076 [.000030] GOLD PLATE IN CONTACT AREA, TIN—LEAD PLATED POSTS.

4

SOLDER PIN POST RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94—1.09 [.037—.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

5.

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE.

7

PART NUMBER IS OBSOLETE.

8

NO CONTACT LUBRICANT

8

60.96
[2.400]

24

64.77
[2.550]

74.93
[2.950]

82.55
[3.250]

75

2—532433—3

—

—

—

—

—

—

2—532433—2

43.18
[1.700]

17

46.99
[1.850]

57.15
[2.250]

64.77
[2.550]

54

2—532433—1

—

—

—

—

—

—

2—532433—0

210.82
[8.300]

83

214.63
[8.450]

224.79
[8.850]

232.41
[9.150]

252

1—532433—9

—

—

—

—

—

—

1—532433—8

—

—

—

—

—

—

1—532433—7

—

—

—

—

—

—

1—532433—6

—

—

—

—

—

—

1—532433—5

213.36
[8.400]

84

217.17
[8.550]

227.33
[8.950]

234.95
[9.250]

255

1—532433—4

200.66
[7.900]

79

204.47
[8.050]

214.63
[8.450]

222.25
[8.750]

240

1—532433—3

187.96
[7.400]

74

191.77
[7.550]

201.93
[7.950]

209.55
[8.250]

225

1—532433—2

175.26
[6.900]

69

179.07
[7.050]

189.23
[7.450]

196.85
[7.750]

210

1—532433—1

162.56
[6.400]

64

166.37
[6.550]

176.53
[6.950]

184.15
[7.250]

195

1—532433—0

149.86
[5.900]

59

153.67
[6.050]

163.83
[6.450]

171.45
[6.750]

180

532433—9

137.16
[5.400]

54

140.97
[5.550]

151.13
[5.950]

158.75
[6.250]

165

532433—8

124.46
[4.900]

49

128.27
[5.050]

138.43
[5.450]

146.05
[5.750]

150

532433—7

111.76
[4.400]

44

115.57
[4.550]

125.73
[4.950]

133.35
[5.250]

135

532433—6

99.06
[3.900]

39

102.87
[4.050]

113.03
[4.450]

120.65
[4.750]

120

532433—5

86.36
[3.400]

34

90.17
[3.550]

100.33
[3.950]

107.95
[4.250]

105

532433—4

78.74
[3.100]

31

82.55
[3.250]

92.71
[3.650]

100.33
[3.950]

96

532433—3

73.66
[2.900]

29

77.47
[3.050]

87.63
[3.450]

95.25
[3.750]

90

532433—2

60.96
[2.400]

24

64.77
[2.550]

74.93
[2.950]

82.55
[3.250]

75

532433—1

E

D

C

B

A

POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± —
± —
± —
± 0.13 [.005]
± —

ANGLES

FINISH

DWN
R.K. SEIFRIED
CHK
G.SKIPPER
APVD

04/09/90
01/21/92
—

NAME

PRODUCT SPEC
—

APPLICATION SPEC
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
532433

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV U

4805 (3/11)