

## Magnastat controlled line voltage soldering irons



### W 61

- 60 W, 230 V



CT 5 Soldering tip series  
page 177

| Order-no.      | Model | Description                                                   |
|----------------|-------|---------------------------------------------------------------|
| T005 61 036 99 | W 61  | Line voltage soldering iron 60 W, 230 V, Magnastat controlled |

### W101

- 100 W, 230 V
- Complete with soldering tip CT6E7 and safety rest



CT 6 Soldering tip series  
page 178

| Order-no.      | Model | Description                                                   |
|----------------|-------|---------------------------------------------------------------|
| T005 61 046 99 | W 101 | Low voltage soldering iron 100 W, 230 V, Magnastat controlled |

### W 101SP

- 100 W, 230 V
- Complete with welding wedge Teflon coated 50 x 40 x 4 mm, twist lock and safety rest

Welding wedge spare  
page 178



| Order-no.      | Model   | Description                                                                                     |
|----------------|---------|-------------------------------------------------------------------------------------------------|
| T005 61 096 99 | W 101SP | Line voltage soldering iron 100 W, 230 V, Magnastat controlled with welding wedge (260°C-295°C) |

### W 201

- 200 W, 230 V
- Complete with soldering tip CT2F7 and safety rest






CT 2 Soldering tip series  
page 179

| Order-no.      | Model | Description                                                    |
|----------------|-------|----------------------------------------------------------------|
| T005 61 056 99 | W 201 | Line voltage soldering iron 200 W, 230 V, Magnastat controlled |

## CT5 Soldering Tip Series



### Soldering Tips for W 61

| Order-no.      | Model          | Description           | Width A |                                                                                      |
|----------------|----------------|-----------------------|---------|--------------------------------------------------------------------------------------|
| 4CT5A6         | <b>CT5 A6</b>  | Chisel tip 310°C      | 1,6 mm  |   |
| 4CT5A7         | <b>CT5 A7</b>  | Chisel tip 370°C      | 1,6 mm  |                                                                                      |
| 4CT5A8         | <b>CT5 A8</b>  | Chisel tip 425°C      | 1,6 mm  |                                                                                      |
| 4CT5B7         | <b>CT5 B7</b>  | Chisel tip 370°C      | 2,4 mm  |                                                                                      |
| 4CT5B8         | <b>CT5 B8</b>  | Chisel tip 425°C      | 2,4 mm  |                                                                                      |
| 4CT5C6         | <b>CT5 C6</b>  | Chisel tip 310°C      | 3,2 mm  |                                                                                      |
| 4CT5C7         | <b>CT5 C7</b>  | Chisel tip 370°C      | 3,2 mm  |  |
| 4CT5C8         | <b>CT5 C8</b>  | Chisel tip 425°C      | 3,2 mm  |                                                                                      |
| 4CT5D7         | <b>CT5 D7</b>  | Chisel tip 370°C      | 4,7 mm  |                                                                                      |
| 4CT5D8         | <b>CT5 D8</b>  | Chisel tip 425°C      | 4,7 mm  |                                                                                      |
| T005 42 107 99 | <b>CT5 AX7</b> | Chisel tip bent 370°C | 1,6 mm  |                                                                                      |
| T005 42 108 99 | <b>CT5 AX8</b> | Chisel tip bent 425°C | 1,6 mm  |                                                                                      |
| T005 42 117 99 | <b>CT5 BX7</b> | Chisel tip bent 370°C | 2,4 mm  |  |
| T005 42 128 99 | <b>CT5 CX8</b> | Chisel tip bent 425°C | 3,2 mm  |                                                                                      |
| T005 42 138 99 | <b>CT5 DX8</b> | Chisel tip bent 425°C | 5,0 mm  |                                                                                      |

# Soldering Tips

## CT6 Soldering Tip Series

### Soldering Tips for W 101

| Order-no.      | Model          | Description           | Width A |                                                                                     |
|----------------|----------------|-----------------------|---------|-------------------------------------------------------------------------------------|
| 4CT6C7         | <b>CT6 C7</b>  | Chisel tip 370°C      | 3,2 mm  |  |
| 4CT6C8         | <b>CT6 C8</b>  | Chisel tip 425°C      | 3,2 mm  |                                                                                     |
| 4CT6D7         | <b>CT6 D7</b>  | Chisel tip 370°C      | 5,0 mm  |                                                                                     |
| 4CT6D8         | <b>CT6 D8</b>  | Chisel tip 425°C      | 5,0 mm  |                                                                                     |
| 4CT6E7         | <b>CT6 E7</b>  | Chisel tip 370°C      | 7,0 mm  |  |
| 4CT6E8         | <b>CT6 E8</b>  | Chisel tip 425°C      | 7,0 mm  |                                                                                     |
| T005 42 307 99 | <b>CT6 CX7</b> | Chisel tip bent 370°C | 3,2 mm  |                                                                                     |
| T005 42 318 99 | <b>CT6 DX8</b> | Chisel tip bent 425°C | 5,0 mm  |                                                                                     |



## Welding wedge

| Order-no.      | Description                                                                                |
|----------------|--------------------------------------------------------------------------------------------|
| T005 11 767 99 | Welding wedge Teflon beschichtet, 50 x 40 x 4 mm (260°C–295°C) for W 101SP with twist lock |
| T005 11 767 74 | Welding wedge PTFEcoated, 50 x 40 x 4 mm                                                   |

## Adapter

For use with LHT tips (page xx) and soldering iron W 101

| Order-no.      | Model        | Description                |
|----------------|--------------|----------------------------|
| T005 61 046 67 | <b>CT6-7</b> | Adapter for LHT tips, 370° |
| T005 61 046 68 | <b>CT6-8</b> | Adapter for LHT tips, 425° |
| T005 61 046 69 | <b>CT6-9</b> | Adapter for LHT tips, 480° |