





注記 NOTES

1. 嵌合相手: 51021 シリーズ MATE WITH: 51021 SERIES
- △ 水平面上においての、ウェハー底面 [W] とソルダーテール及び
フィッティングネイル底面とのズレ量を示す。
MISALIGNMENT OF SOLDER TAIL & FITTING NAIL FROM [W]
- △ 偶数極にのみ適用。APPLY EVEN CIRCUIT PRODUCTS.
- △ ロック窓は、2、3極は1ヶ所、4極以上は2ヶ所とする。
LOCKING WINDOW: ONE PLACE FOR 2&3 CKTS.
TWO PLACES FOR MORE THAN 4 CKTS.



23.9	23.5	20.5	18.6	19.3	17.5	53398-1510	15
22.65	22.25	19.25	17.35	18.05	16.25	-1410	14
21.4	21	18	16.1	16.8	15	-1310	13
20.15	19.75	16.75	14.85	15.55	13.75	-1210	12
18.9	18.5	15.5	13.6	14.3	12.5	-1110	11
17.65	17.25	14.25	12.35	13.05	11.25	-1010	10
16.4	16	13	11.1	11.8	10	-0910	9
15.15	14.75	11.75	9.85	10.55	8.75	-0810	8
13.9	13.5	10.5	8.6	9.3	7.5	-0710	7
12.65	12.25	9.25	7.35	8.05	6.25	-0610	6
11.4	11	8	6.1	6.8	5	-0510	5
10.15	9.75	6.75	4.85	5.55	3.75	-0410	4
8.9	8.5	5.5	3.6	4.3	2.5	-0310	3
7.65	7.25	4.25	2.35	3.05	1.25	53398-0210	2
F	E	D	C	B	A	ENG. NO.	極数 NO. OF CKTS.

F	変更 REVISED	WC2000-0636	K.K.	00/3/30
E	変更 REVISED	WC800-08	M.F.	91/7/5
D	変更 REVISED	U31030	H.H.	93/10/13
C	変更 REVISED	U30753	K.T.	93/7/29
B	変更 REVISED	U30610	K.T.	93/6/18
A	変更 REVISED	U30230	K.T.	93/3/10
0	新規作成 RELEASED	U20942	K.T.	92/10/12
角 度	ANGLE	±3°		
30°以上 OVER		±0.3		
10°以上 30°未満 OVER		±0.25		
10°未満 OVER		±0.2		
未過 UNDER				
公差 TOLERANCES	記号 LTR	変更内容 REVISION RECORD	DR. CHK.	日付 DATE

材料 MATERIAL	図中参照 SEE DRAWING
仕上げ FINISH	—
適用電線範囲 WIRE RANGE	—
被覆外径 INS. RANGE	—
DRAWN BY '92/10/12 K.T.OJO	CHK'D BY '00/3/30 T.YAMAGUCHI
APP'D BY '00/3/30 M.FUKUSHIMA	尺度 SCALE
材料 MATERIAL	図中参照 SEE DRAWING
仕上げ FINISH	—
適用電線範囲 WIRE RANGE	—
被覆外径 INS. RANGE	—
DRAWN BY '92/10/12 K.T.OJO	CHK'D BY '00/3/30 T.YAMAGUCHI
APP'D BY '00/3/30 M.FUKUSHIMA	尺度 SCALE
材料 MATERIAL	図中参照 SEE DRAWING
仕上げ FINISH	—
適用電線範囲 WIRE RANGE	—
被覆外径 INS. RANGE	—
DRAWN BY '92/10/12 K.T.OJO	CHK'D BY '00/3/30 T.YAMAGUCHI
APP'D BY '00/3/30 M.FUKUSHIMA	尺度 SCALE

MOLEX-JAPAN CO.,LTD.
日本モレックス株式会社

REVISE ONLY ON CAD SYSTEM

TITLE 名称

1.25 WIRE TO BOARD CONN.
WAFER ASS'Y FOR SMT (ST.)

DWG. NO.


SD-53398-**-10

REV


F

10 9 8 7 6 5 4 3 2 1



引き出し方向
PULL OUT DIRECTION



DETAIL "F"




16幅テープ
(TAPE WIDTH:16)



NOTES

- 梱包数量:1000個/リール
NUMBER OF CONNECTOR:1000PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- トップテープの剥離強度:0.6±0.35N(60±35gf) (剥離方向は下図参照)
PEELING OFF FORCE OF TOP TAPE:0.6±0.35N(60±35gf)
(PEELING DIRECTION IS SHOWN IN FOLLOWING FIG.)

<剥離速度:300mm/min(参考)>
PEELING SPEED:300mm/min.
(REFERENCE)



- 53398-**10の詳細寸法については図面SD-53398-**10を参照下さい。
RE DETAILED DIMENSIONS,SEE SD-53398-**10.

- 材料 (MATERIAL)
キャリアテープ(CARRIER TAPE):ポリプロピレン(POLYPROPYLENE)
トップテープ (TOP TAPE): PET ,PE ,PEF
リール (REEL):ポリスチレン (P S) <リサイクル材含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>


16	17.4	3.7	9.5	5.8	53398-0390	3
キャリアテープ幅 CARRIER TAPE WIDTH	D	2.45	8.25	4.55	53398-0290	2
		(C)	(B)	(A)	ENG. NO.	種数 CKT.

DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM ONLY	---	METRIC	

DRAWN BY K. TOJO	DATE '93/04/13	TITLE 1.25 W/B CONN. WAFER ASS'Y FOR SMT. EMBOSSD TAPE PACKAGE
CHECKED BY YAMAGUCHI	DATE '00/12/08	
APPROVED BY FUKUSHIM	DATE '00/12/08	MOLEX INCORPORATED


MATERIAL NO.	DOCUMENT NO.	SHEET NO.
SEE CHART	SD-53398-**90	1 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



32	33.4	16.2	22	18.3	53398-1390	13
		14.95	20.75	17.05	▲ -1290	12
		13.7	19.5	15.8	▲ -1190	11
24	25.4	12.45	18.25	14.55	▲ -1090	10
		11.2	17	13.3	▲ -0990	9
		9.95	15.75	12.05	▲ -0890	8
		8.7	14.5	10.8	▲ -0790	7
		7.45	13.25	9.55	▲ -0690	6
		6.2	12	8.3	▼ -0590	5
		4.95	10.75	7.05	53398-0490	4
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	ENG. NO.	極数 CKT.

REVISED EC NO: T DRAWN: MERIGUCHI CHKD: K. ASAKAWA APPR: S. ICHIKAWA 2004/07/27 2004/07/28 2004/07/30	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY K. TOJO	DATE '93/04/13	TITLE 1.25 W/B CONN. WAFER ASS'Y FOR SMT. EMBOSSED TAPE PACKAGE				
		10 OVER 30 UNDER	± 0.25	CHECKED BY YAMAGUCHI	DATE '00/12/08					
		30 OVER	± 0.3	APPROVED BY FUKUSHIM	DATE '00/12/08					
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-53398-**90		2 OF 3			
REV		SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								



引き出し方向
PULL OUT DIRECTION

44幅テープ
(TAPE WIDTH:44)

REVISED	2004/07/27	2004/07/28	2004/07/30
EC NO:	DRWN:MERIGUCH	CHKD:K.ASAKAW	APPR:SIKIKAW
DESCRIPTION			
REV			

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
K. TOJO	'93/04/13
CHECKED BY	DATE
YAMAGUCH	'00/12/08
APPROVED BY	DATE
FUKUSHIM	'00/12/08
MATERIAL NO.	
SEE CHART	
SIZE	
A3	

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
---	METRIC	◎	□
TITLE			
1.25 W/B CONN. WAFER ASS'Y FOR SMT. EMBOSSED TAPE PACKAGE			
MOLEX INCORPORATED			
DOCUMENT NO.			SHEET NO.
SD-53398-**90			3 OF 3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			