

D3FS4A

40V 2.6A


FEATURES

- Small SMT
- Tj150°C
- Low VF=0.45V
- PRRSM avalanche guaranteed

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified TI=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		40	V
Repetitive Peak Surge Reverse Voltage	VRRSM	Pulse width 0.5ms, duty 1/40	45	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load Ta=34°C On alumina substrate	2.6	A
		50Hz sine wave, R-load Ta=30°C On glass-epoxy substrate	1.9	
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=125°C	150	A
Repetitive Peak Surge Reverse Power	PRRSM	Pulse width 10 μs, Tj=25°C	330	W

● Electrical Characteristics (If not specified TI=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.6A, Pulse measurement	Max.0.45	V
Reverse Current	IR	VR=VRM, Pulse measurement	Max.5	mA
Junction Capacitance	Cj	f=1MHz, VR=10V	Typ.340	pF
Thermal Resistance	θjl	junction to lead	Max.23	°C/W
	θja	junction to ambient On alumina substrate	Max.80	
		junction to ambient On glass-epoxy substrate	Max.115	

D3FS4A

Forward Voltage




D3FS4A Junction Capacitance




D3FS4A

Reverse Current




D3FS4A

Reverse Power Dissipation




$T_j = 150^\circ\text{C}$




D3FS4A

Forward Power Dissipation




$T_j = 150^\circ\text{C}$




D3FS4A

Derating Curve




$V_R = 10V$




D3FS4A

Derating Curve




$V_R = 10V$



D3FS4A

Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

